Product data sheet Characteristics

NSYCAG33LP

Airing grille cut-out diameter 33mm IP45





Main

Range	ClimaSys
Product	ClimaSys CA
Range compatibility	Thalassa PLS Thalassa PLM Thalassa TBS
Product or Component Type	Plastic ventilation louvre
Accessory / separate part category	Thermal management accessory
Accessory / separate part destination	ClimaSys ventilation system
Mounting position	Vertical
Fixing Mode	By screws
Device composition	2 plastic louvre

Complementary

Material	Polyamide 6	
Color	Gray RAL 7035)	
Cut-out dimensions	33 mm	
Height	External 2.72 in (69 mm)	
Width	External 1.85 in (47 mm)	
Depth	External 0.89 in (22.5 mm)	
IP degree of protection	IP44	

Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES	
Discount Schedule	ES1	
GTIN	3606480151910	
Nbr. of units in pkg.	1	
Package weight(Lbs)	0.92 oz (26 g)	
Returnability	No	
Country of origin	ES	

Packing Units

Unit Type of Package 1	PCE	
Package 1 Height	0.79 in (2 cm)	
Package 1 width	1.77 in (4.5 cm)	
Package 1 Length	2.76 in (7 cm)	
Unit Type of Package 2	BB1	
Number of Units in Package 2	2	
Package 2 Weight	2.02 oz (57.2 g)	
Package 2 Height	1.57 in (4 cm)	
Package 2 width	1.77 in (4.5 cm)	
Package 2 Length	2.76 in (7 cm)	

Offer Sustainability

- · · · · · · · · · · · · · · · · · · ·	
Sustainable offer status	Green Premium product
REACh Regulation	☑ REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	₫Yes
China RoHS Regulation	☐ China RoHS Declaration

Contractual warranty

Warranty	18 months