

Perfect for under cabinet domestic and some light commercial applications.

LED SUPER FLAT STRIP LIGHTS

Ultra low power consumption with excellent light output. The inclusion of a link lead and butt connector allows continuous linear, spaced linear or radial installations.


- Aluminum and polycarbonate construction
- Ultra-bright warm white LEDs for a pleasing lighting effect (3000K colour temperature)
- Super flat design
- 9 LED strip output: 2.2W
- 15 LED strip output: 3.6W
- Reeded diffuser for soft diffused light
- Fixing clips included for under-cabinet or wall installation
- 300mm link lead and butt connector included: allowing flexible linking options
- 5 year warranty

36W CONSTANT VOLTAGE DRIVER (SFLDR36)


- For use with SFLWW range only
- Allows multiple strip lights to be linked
- Includes 0.5m mains cable & 2m fitting supply cable with amp-plug connector: easy installation
- Allows any combination of SFLWW9 & SFLWW15 upto a maximum power load of 36W: simply link the first fitting to the driver and subsequent fittings to each other

- Strip lights = M.O.M: 1 / O.P.Q: 10
- Driver = M.O.M: 1 / O.P.Q: 20

2 x surface mounting clips and 2 x horizontal mounting clips included



Butt connector included



300mm link lead included


9 LED

15 LED

SUPER FLAT PROFILE



ACTUAL SIZE SHOWN



| Code | Version | Colour | Rated Wattage | Colour Temp. | Lumens | Avg. Rated Life (Hrs) | IP Rating |
|---------|------------|-------------|---------------|--------------|--------|-----------------------|-----------|
| SFLWW9 | 9 LED | Matt Silver | 2.2W | 3000K | 230 lm | 20,000 hrs | IP20 |
| SFLWW15 | 15 LED | | 3.6W | | 360 lm | | |
| SFLDR36 | 36W Driver | | | | | | |

Eterna[®]
Everyday Lighting For Professionals

| SPECIFICATIONS: | SFLWW9 | SFLWW15 |
|--|-------------------------------|-------------------------------|
| Lumens total flux | 230 lm | 360 lm |
| Lumens 120° flux | 220 lm | 340 lm |
| Rated Wattage | 2.2W | 3.6W |
| Rated luminous flux | 220 lm | 340 lm |
| Nominal life time of the lamp | 20,000 hrs | 20,000 hrs |
| Colour temperature | 3000K | 3000K |
| Number of switching cycles before premature lamp failure | 10,000 | 10,000 |
| Warm-up time up to 60 % of the full light output | Instant full light | Instant full light |
| Dimmable | No | No |
| Lamp dimensions (mm) | 350 x 18.6 | 550 x 18.6 |
| Nominal beam angle | 120° | 120° |
| Rated power | 2.2W | 3.6W |
| Rated lamp lifetime | 20,000 | 20,000 |
| Lamp power factor | 0.9 | 0.9 |
| Lumen maintenance factor at end of nominal life | 70% | 70% |
| Starting time | <0.5s | <0.5s |
| Colour rendering | 80 | 80 |
| Colour consistency | Within 6 step Macadam ellipse | Within 6 step Macadam ellipse |
| Rated peak intensity | 79cd | 122cd |
| Rated beam angle | 120° | 120° |