

**SUNSET ST64 BULB B22 170LM 2.5W 1800K NON-DIMM 300 BEAM AMBER
INTEGRAL**

ILST64B22N002



Create a relaxing ambience with an ultra-warm (1800K), energy-saving LED filament lamp. The Sunset range has a retro look with tinted amber glass and an eye-catching vintage design. Built using the latest LED filament technology to deliver an A+ energy rating and 93% energy savings compared to the incandescent lamp it replaces. Enjoy the classic aesthetic look but with an improved lifetime of 15,000 hours.

Details

Quick Order Code:	201747
Barcode:	5055788218500
Category:	Lamps
Range Name:	Sunset
Product Type:	Vintage Decorative
Product Body Finish:	Amber
Market Segment:	Commercial indoor, Residential indoor, Vintage Decorative
Finish:	Amber
Warranty (Years):	2
CE RoHS:	Yes

Physical Data

Product Length (mm):	138
Product Width (mm):	64
Product Weight (g):	47
Material:	Glass
Base Term:	Bayonet cap
Bulb Base:	B22
Construction:	Glass shell, filament strip
Globe Finish:	Clear
Globe Type:	ST64
Bulb Fixing:	Pendant, Chandelier, Wall
Bulb or Luminaire Shape:	Oval
Placement / Application:	Indoor, General Lighting

Electrical Data


Power (W):	2.5
Power Consumption (w):	2.5
Power Factor:	0.5
Wattage equivalent (W):	40
Amperage (mA):	41
Dimming:	Non-Dimmable
Driver Included:	Yes
Electric Current:	AC
EN:	EN-62560
LVD Certified:	Yes

Light Data

Luminous Flux in Lumens (lm):	170
Luminous efficacy (lm/W):	68
Correlated Colour Temperature (CCT) (K):	1800
Colour Temperature:	1800K - Ultra Warm
Colour Temperature Name:	Ultra Warm
Beam Angle:	300
Colour Rendering Index (CRI):	80
Instant on (Less than 1 second):	Yes
LED Type:	Filament
Lifetime (hours):	15000
Switching Cycles:	7500

Environment

EN:	EN-62560
LVD Certified:	Yes
CE RoHS:	Yes
Energy Rating:	A+
Hg 0% (Mercury Free):	Yes
IP Rating (Ingress Protection):	IP20
Lowest Operating Temperature (°C):	-20
Maximum Operating Temperature (°C):	45



Portal.integral-led.com

Packaging

Product Design And Specification Subject To Change Or Modification Without Notice. Image For Illustration Only. E&OE

Package Weight (g):	90
Package Length (mm):	153
Package Width (mm):	72
Package Depth (mm):	72
Qty per euro pallet:	900