

GU10 BULB 390LM 4W 4000K NON-DIMM 36 BEAM INTEGRAL

ILGU10NE103



The Integral LED Classic GU10 range offers a fantastic ratio of value and performance. By incorporating a stylish engineered lens in an affordable GU10, the Classic offers directional light with a beam angle that closely mirrors that of familiar halogen lamps along with all the energy-saving and long-life benefits of LED.

Details

Quick Order Code:	522628
Barcode:	5055788241003
Category:	Lamps
Range Name:	Classic
Product Type:	GU10
Product Body Finish:	Matt white
Market Segment:	Commercial indoor, Residential indoor
Warranty (Years):	2
CE RoHS:	Yes

Physical Data

Product Length (mm):	54
Product Width (mm):	50
Product Weight (g):	25
Optic:	Designed to give a Classic Look
Material:	Plastic and Aluminium heat-sink, Injection moulded diffuser
Base Term:	GU10
Bulb Base:	GU10
Construction:	Plastic White and "Classic look" difuser lens
Bulb Fixing:	Downlight
Bulb or Luminaire Shape:	Round
Placement / Application:	Indoor, General Lighting
Spot Type:	SMD with "COB like effect"

Electrical Data

Power (W):	4
Power Consumption (w):	4
Power Factor:	0.4


Wattage equivalent (W):	52
Amperage (mA):	34
Dimming:	Non-Dimmable
Driver Included:	Yes
Electric Current:	AC
EN:	EN-62560
LVD Certified:	Yes

Light Data

Luminous Flux in Lumens (lm):	390
Luminous efficacy (lm/W):	98
Peak Intensity (Cd):	750
Correlated Colour Temperature (CCT) (K):	4000
Colour Temperature:	4000K - Cool White
Colour Temperature Name:	Cool White
Beam Angle:	36
Colour Rendering Index (CRI):	80
Instant on (Less than 1 second):	Yes
LED Type:	Surface mounted device (SMD)
Lifetime (hours):	15000
Switching Cycles:	7500
Useful Lumens (lm):	360

Environment

EN:	EN-62560
LVD Certified:	Yes
CE RoHS:	Yes
Energy Rating:	A++
Hg 0% (Mercury Free):	Yes
Lowest Operating Temperature (°C):	-20
Maximum Operating Temperature (°C):	40



Packaging

Package Weight (g):	50
----------------------------	----

Portal.integral-led.com

Product Design And Specification Subject To Change Or Modification Without Notice. Image For Illustration Only. E&OE

Package Length (mm):	55
Package Width (mm):	55
Package Depth (mm):	60