
Product data sheet



🚺 <u>brannan.co.uk</u>

ELECTRONIC TEST THERMOMETER WITH PROBE

Electronic thermometer with robust stainless steel probe. Temperature hold and max min functions. Supplied with hanger, stand and magnetic fixtures.



Product features:

- Wide measurement range
- Max/Min temperature memory
- Data hold function
- Large, clear LCD
- Hanger, stand and magnet fixture

Product specifications:

Measuring range:	-20°C to 200°C/-58°F to 392°F
Accuracy:	±1°C (19.9°C to 199°C)
	\pm 1°C (-50°C to 100°C) otherwise \pm 2.5°C
Resolution:	±1°C (19.9°C to 199°C) otherwise 1°C
Sampling rate:	1 second
Battery:	1рс х ААА
CE/ROHS/WEEE:	Compliant
Hazard information (SDS):	See brannan.co.uk for information
Cable:	1.5m
Probe length:	125mm
LCD dimensions:	16mm x 36mm
Product dimensions:	Net: 97mm x 65mm x 20mm (main unit)
	Gross: 220mm x 112mm x 31mm
Product weight:	Net: 96g (including batteries)
	Gross: 137g (including 41g box)

Description	Barcode	Product No
Test thermometer	5 011405 386502	38/650/0
Replacement probe	-	38/650/1



View me on the website



Brannan

brannan.co.uk

Measurement for life.