



Vario-Line Cable Box

- Housing made of break-resistant plastic.
- Practical carrying handle.
- Twin feet ensure excellent stability.
- Easy to wind and rewind.
- With 3-way socket outlet 13 A BS with self-closing cover providing protection against dust and contamination.
- With thermal cut-out protection against overheating.



TECHNICAL DATA

Product number	1098203	1108563	1093203	1108903
EAN	4007123133048	4007123140831	4007123641482	4007123140848
UP	5	5	5	5
Cable length	5 m	10 m	10 m	15 m
Cable designation	H05VV-F 3G1,5	H05VV-F 3G1,5	H05VV-F 3G1,5	H05VV-F 3G1,5
Cable quality	PVC	PVC	PVC	PVC
Cable colour	black	black	black	black
Plug system plug	Type G (GB)	Type G (GB)	Type G (GB)	Type G (GB)
Max. current carrying capacity	13 A	13 A	13 A	13 A
Colour	blue/black	blue/black	black	blue/black



TECHNICAL DATA

Product number	1094203	1108553	1108203
EAN	4007123641468	4007123147595	4007123142019
UP	5	5	5
Cable length	15 m	10 m	20 m
Cable designation	H05VV-F 3G1,5	H05VV-F 3G1,0	H05VV-F 3G1,0
Cable quality	PVC	PVC	PVC
Cable colour	black	black	black
Plug system plug	Type G (GB)	Type G (GB)	Type G (GB)
Max. current carrying capacity	13 A	10 A	10 A
Colour	black	light grey/black	light grey/black

10A

10A