

# **EMERGENCY CONVERSION KIT 6.4V 1.5Ah LiFePO4 3.5W 250V MAX. 3HR FOR 240V MAINS VOLTAGE LUMINAIRES**

ILEMPK076



This Emergency Conversion Kit will convert compatible panels and downlights (up to 25W) into emergency luminaires. It will provide emergency lighting for 3 hours.

## **Details**

<b>Product Body Finish:</b>	Matt white
<b>Warranty (Years):</b>	1
<b>CE RoHS:</b>	Yes

## **Physical Data**

<b>Product Length (mm):</b>	199
<b>Product Depth (mm):</b>	24
<b>Product Width (mm):</b>	55
<b>Product Weight (g):</b>	1.22
<b>Bulb or Luminaire Shape:</b>	Linear
<b>Luminaire Fixing:</b>	In Ceiling

## **Electrical Data**

<b>Power Consumption (w):</b>	3.5
<b>Input Voltage (V):</b>	220-240
<b>Battery Configuration:</b>	6.4V 1.5Ah LiFePO4 3.5W
<b>Dimming:</b>	Dimmable
<b>Driver Included:</b>	Yes
<b>Electric Current:</b>	AC
<b>EN:</b>	EN-62560
<b>LVD Certified:</b>	Yes

## **Light Data**

<b>Instant on (Less than 1 second):</b>	Yes
<b>LED Type:</b>	Per Luminaire
<b>Lifetime (hours):</b>	50000

## **Environment**

EN:	EN-62560
LVD Certified:	Yes
CE RoHS:	Yes
IP Rating (Ingress Protection):	IP20
Lowest Operating Temperature (°C):	0
Maximum Operating Temperature (°C):	60

### **Packaging**

Package Weight (g):	1220
Package Length (mm):	199
Package Width (mm):	55
Package Depth (mm):	24