

SPECIFICATION SHEET

Product Code

CL019

Description

10AX 4 Gang 2 Way Plate Switch (Modular) with Mounting Box



General Information	
Dimensions	140mm x 80mm
Material composition	Rear Housing: Urea Front Plate and Back Box: Steel Terminals: Brass Earth Strap: Mild Steel Terminal Screws: Steel and Yellow Passivated Silver "on-lay" copper/brass contacts.
Back Box Depth	40mm
Cable Size	4 x 1.5mm ² or 2 x 2.5mm ²
Terminal Size	Live: 3.5mm Earth: 3.5mm Knockouts: 20mm
Load Rating	10AX (Suitable for Inductive loads)
Modular	Yes
Gang	4
2 Way	Yes
Intermediate	No
Warranty	10 Years Domestic

Standards	BS EN 60669
-----------	-------------

Additional Information	Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram supplied with the relevant product. Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal. Interchangeable with switches in the MiniGrid system. 
------------------------	---