



TECHNICAL INFORMATION

Watts:	45
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	Silver
Body Type:	Aluminium
Operation Temperature:	-20°C to +45°C
Rated Load:	Max 29-45W
Dimension:	455x52x33mm
Output Voltage:	DC:30-42V
Emergency Standby Watts:	10
Battery Type:	Ni-Cd 7.2V, 4000mAh
Charging Time:	24 hours
Working Time:	3 Hours
Emergency Operation Time:	>3 Hours



FEATURES

- Reliable 3 Hours emergency operation time
- Sealed Ni-cd battery guarantees high efficiency and lifecycle
- Output power max 10W
- AC wire Length 35cm - DC wire length 40 cm
- Wire length of LED Indicator and Test button 60 cm

CE/EMC

CE/LVD



EMERGENCY PACK-29W TO 45W | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 60303 - 1567 1246

[View more details](#)



PACKAGING

Gross Weight (Kgs): 1.09
Unit CBM: 0.003276
Dimension: 455x52x33mm

MASTER BOX PACKAGING

Box Qty: 12
Qty Per Pallet: 480
Length (Box) mm: 510
Width (Box) mm: 75
Height (Box) mm: 45

LISTING DETAILS

Commodity Code: 8504409090
Ean Code: 3800157617451