



TECHNICAL INFORMATION

Watts:	6
Lumens:	300
Input Power:	AC:220-240V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	PC
LED Chip Type:	SMD
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Color Temperature:	6000K
Dimension:	296x75x272mm
Battery Type:	Ni-Cd 9.6V, 2200mAh
Charging Time:	24 Hours(Initial charge 36 hours)
Battery Charging Current:	150-180mA
Battery Discharge Current:	400-600mA
Emergency Operation Time:	>3 Hours



IP65
RATING



2 YEAR
WARRANTY

FEATURES

- Wall mounted emergency twin spotlight
- Adjustable heads
- Fitted with high efficiency LED Chips
- High-performance Ni-Cd batteries made for Longevity & low maintenance.
- Green Light Indicator
- Reliable Emergency backup of 3 hours.
- Non maintained operation
- IP65 Protection perfect for outdoor use

CE/EMC

CE/LVD



EMERGENCY TWIN SPOTLIGHT | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 80981 - 1253 940

[View more details](#)

EMERGENCY TWIN SPOTLIGHT

— Wall-Mounted Installation



PACKAGING

Gross Weight (Kgs): 1.78

Unit CBM: 0.00965

Dimension: 296x75x272mm

MASTER BOX PACKAGING

Box Qty: 5

Qty Per Pallet: 35

LISTING DETAILS

Commodity Code: 9405104090

Ean Code: 3800157639705