



TECHNICAL INFORMATION

Watts:	10
Lumens:	800
Input Power:	AC:220-240V, 50Hz
Long Life:	30,000 Hours
Unit Color:	Black
Body Type:	Die Cast Aluminium
PF:	>0.7
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	100°
Color Temperature:	4000K
Dimension:	114.5x54.86x153.78mm
Sensor Type:	PIR
Detection Distance:	2-8m

ROTATABLE PIR SENSOR PRO | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 437 - 930 938

[View more details](#)



FEATURES

- PIR Sensor Floodlight built with adjustable sensor head
- Designed with Manual Override functionality
- IP65 protection - Built with 1 Meter wire.
- Designed with high efficiency LED Samsung Chips
- Built in driver - no external power supply required
- Built Strong and durable with Die Cast Aluminium - Corrosion resistant design
- Suitable for driveways, gardens, patio, building, security lighting etc.

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs): 0.44
Unit CBM: 0.001764
Dimension: 114.5x54.86x153.78mm

MASTER BOX PACKAGING

Box Qty: 20
Qty Per Pallet: 600
Length (Box) mm: 65
Width (Box) mm: 135
Height (Box) mm: 170

LISTING DETAILS

Commodity Code: 9405421000
Ean Code: 3800157630931