

TECHNICAL INFORMATION

| | |
|--------------------|-------------------|
| Watts: | 24 |
| Lumens: | 2880 |
| Input Power: | AC:220-240V, 50Hz |
| Long Life: | 30,000 Hours |
| Unit Color: | White |
| Body Type: | Aluminium |
| PF: | >0.5 |
| LED Chip Type: | SMD-Samsung Chip |
| CRI: | >80 |
| Dimmable: | No |
| Beam Angle: | 120° |
| Color Temperature: | 4000K |
| Dimension: | 1166x60x75mm |
| lumens per watt: | 120 |


LED BATTEN FITTINGS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 20066 - 1456 940

[View more details](#)



LED BATTEN FITTING



FEATURES

- LED chip by Samsung delivering high-performance light output 120LM/W
- Designed with quick connector for easy wiring
- Built with safety straps for hanging and handsfree maintenance
- Strong and sturdy Aluminium body
- Direct AC power no ballast or starter required
- Suitable for commercial lighting, residential lighting, office, supermarkets, shop, hotels & similar environment



PACKAGING

Gross Weight (Kgs): 1.51
Unit CBM: 0.00689
Dimension: 1166x60x75mm

MASTER BOX PACKAGING

Box Qty: 12
Qty Per Pallet: 240
Length (Box) mm: 63
Width (Box) mm: 79
Height (Box) mm: 1171

LISTING DETAILS

Commodity Code: 9405104090
Ean Code: 3800157656719