

TECHNICAL INFORMATION

Watts:	24
Lumens:	2880
Input Power:	AC:220-240V, 50Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	Aluminium
PF:	>0.5
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Dimmable:	No
Beam Angle:	120°
Color Temperature:	6400K
Dimension:	1166x60x75mm
lumens per watt:	120


LED BATTEN FITTINGS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 20067 - 1456 940

[View more details](#)



LED BATTEN FITTING



FEATURES

- LED chip by Samsung delivering high-performance light output 120LM/W
- Designed with quick connector for easy wiring
- Built with safety straps for hanging and handsfree maintenance
- Strong and sturdy Aluminium body
- Direct AC power no ballast or starter required
- Suitable for commercial lighting, residential lighting, office, supermarkets, shop, hotels & similar environment



PACKAGING

Gross Weight (Kgs): **1.51**
Unit CBM: **0.00689**
Dimension: **1166x60x75mm**

MASTER BOX PACKAGING

Box Qty: **12**
Qty Per Pallet: **240**
Length (Box) mm: **63**
Width (Box) mm: **79**
Height (Box) mm: **1171**

LISTING DETAILS

Commodity Code: **9405104090**
Ean Code: **3800157656726**