

TECHNICAL INFORMATION

Watts:	50
Lumens:	6000
Input Power:	AC:220-240V, 50Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	Aluminium
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Beam Angle:	120°
Color Temperature:	4000K
Dimension:	1466x60x75mm
lumens per watt:	120


LED BATTEN FITTINGS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 20072 - 933 940

[View more details](#)



LED BATTEN FITTING



FEATURES

- LED chip by Samsung delivering high-performance light output 120LM/W
- Designed with quick connector for easy wiring
- Built with safety straps for hanging and handsfree maintenance
- Strong and sturdy Aluminium body
- Direct AC power no ballast or starter required
- Suitable for commercial lighting, residential lighting, office, supermarkets, shop, hotels & similar environment



PACKAGING

Gross Weight (Kgs): 1.88
Unit CBM: 0.008578
Dimension: 1466x60x75mm

MASTER BOX PACKAGING

Box Qty: 10
Qty Per Pallet: 140
Length (Box) mm: 63
Width (Box) mm: 79
Height (Box) mm: 1471

LISTING DETAILS

Commodity Code: 9405104090
Ean Code: 3800157656771