



## TECHNICAL INFORMATION

Watts:	14
Lumens:	1400
Shape:	Round
Input Power:	AC:200-240V, 50/60Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	PC
PF:	>0.5
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Beam Angle:	120°
Color Temperature:	3IN1
Dimension:	315x75mm
Type:	Light

## BULKHEAD-CCT | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 20088 - 1557 940

[View more details](#)



## FEATURES

- Uses High Quality Power Driver and Samsung LED Chip
- Built-in switch for CCT changing
- Hinged LED gear tray for easy installation
- Withstands weather, dust and vandalism
- Applications - Passage, Exterior walls, Airport, Malls, Security Lighting etc



## PACKAGING

Gross Weight (Kgs):	1.01
Unit CBM:	0.00948
Dimension:	315x75mm

## MASTER BOX PACKAGING

Box Qty:	10
Qty Per Pallet:	120
Length (Box) mm:	325
Width (Box) mm:	78
Height (Box) mm:	325

## LISTING DETAILS

Commodity Code:	9405104090
Ean Code:	3800157657372