



TECHNICAL INFORMATION

Watts:	4
Lumens:	350
Shape:	Candle
Input Power:	AC:220-240V, 50Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	Glass
PF:	>0.4
LED Chip Type:	Filament
CRI:	>80
Operation Temperature:	-25°C to +50°C
Dimmable:	No
Beam Angle:	300°
Color Temperature:	6400K
Equivalence Watts:	35
Dimension:	35x100mm



FEATURES

- Modern frost filament Filament technology for better reliability and durability
- Replaces 35 watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps.
- Designed for E14 standard holder
- Excellent power factor and integrated IC driver
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

CE/EMC

CE/LVD



FROST CANDLE E14 | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 71031 - 1438 940

[View more details](#)

PACKAGING

Gross Weight (Kgs): 0.022
Unit CBM: 0.0001225
Dimension: 35x100mm

MASTER BOX PACKAGING

Box Qty: 100
Qty Per Pallet: 7000
Length (Box) mm: 35
Width (Box) mm: 35
Height (Box) mm: 100

LISTING DETAILS

Commodity Code: 8539520000
Ean Code: 3800157624244