



KRAMER

900xl

Stereo Power Amplifier (10 Watts per Channel)

| Speakers



The 900xl is a high-performance power amplifier for line level stereo audio signals. The unit accepts unbalanced audio signals on either of two RCA or 3.5mm connectors and delivers a speaker output of 10 watts RMS per channel into a 4Ω load

FEATURES

High Efficiency - Class D operation

S/N Ratio - 60dB

Control - Volume & input selection from front panel & RS-232

Compact Kramer TOOLS™ - 3 units can be rack mounted side-by-side in a 1U rack space with the recommended rack adapter



KRAMER

TECHNICAL SPECIFICATIONS

INPUTS:	1 unbalanced stereo audio on a 3.5mm mini jack connector, 1 unbalanced stereo audio on RCA connectors
OUTPUT:	1 stereo differential speaker output
OUTPUT POWER:	2x10W (4Ω)
INPUT SENSITIVITY:	460mV
OUTPUT MUSIC POWER:	2x40W (4Ω)
BANDWIDTH (-3dB):	25kHz
S/N RATIO:	85dB @1kHz, 0dBu output
CONTROLS:	Gain range: -14 to +32dB at high-gain; -21 to +20dB at low-gain
COUPLING:	Input: AC; output: DC
AUDIO THD + NOISE:	0.6% @0dBu output
AUDIO 2nd HARMONIC:	0.35% @0dBu output
POWER CONSUMPTION:	12V DC, 2.0A
OPERATING TEMPERATURE:	0° to +40°C (32° to 104°F)
STORAGE TEMPERATURE:	-45° to +72°C (-49° to 162°F)
HUMIDITY:	10% to 90%, RHL non-condensing
INCLUDED ACCESSORIES:	Power supply
Product Dimensions	12.00cm x 7.15cm x 2.44cm (4.72" x 2.81" x 0.96") W, D, H
Product Weight	0.0kg (0.0lbs) approx
Shipping Dimensions	15.70cm x 12.00cm x 8.70cm (6.18" x 4.72" x 3.43") W, D, H
Shipping Weight	0.6kg (1.4lbs) approx

