



- RCBO to BS EN 61009 - Type A (AC Waveform + Pulsating DC) / 10kA to BS EN 60898-1 @ 240V AC
- C curve trip characteristic (5-10In)
- Neutral & Earth Tail lengths = 600mm

Product Specification Data

Revision Date: 15/10/2021

Number of poles	1
Rated voltage	230 V
Rated current	40 A
Mounting method	DIN Rail
Leakage current type	A
Short-time delayed tripping	No
Short-circuit breaking capacity (Icw)	10 kA
Frequency	50/60 Hz
Additional equipment possible	Yes
With interlocking device	No
Width in number of modular spacings	1
Product Standard/s	BS EN 60898-1, 2
Terminal Capacity L&N	16 mm ²
CE Conformity	Yes
WEEE Symbol	Yes
UKCA Conformity	Yes

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this datasheet, specifications and performance data are constantly changing. Latest details can be obtained from the Electrium website.