



- Screwless Plate
- Triple Pole Switching
- Satin Chrome Finish

Product Specification Data		Revision Date: 15/10/2021
Product Standard/s	BS EN 60669-1, BS EN 60947-3	
Terminal Capacity L&N	4 x 1.0, 3 x 1.5, 1 x 2.5 mm ²	
Frequency	50 Hz	
Printing	Isolator Symbol, On, Off	
CE Conformity	Yes	
WEEE Symbol	Yes	
UKCA Conformity	Yes	
Wiring system	3-pole switch	
Method of operation	Rocker/button	
Assembly arrangement	Control element	
Number of modules (module system)	0	
Push button switch	Yes	
Number of rockers	1	
Mounting method	Flush mounted (plaster)	
Type of fastening	Screw mounting	
With mounting plate	Yes	
Material	Metal	
Material quality	Other	
Halogen free	Yes	
Surface protection	Other	
Surface finishing	Matt	
Colour	Stainless Steel	
Illumination	No	
Function lighting	Other	
Type of lighting	Not included	
Suitable for degree of protection (IP)	IP2X	
Nominal voltage	250 V	
Rated current	6 A	
Connection type	Screwed terminal	

Width of device	88 mm
Height of device	88 mm
Min. depth of built-in installation box	25 mm

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this datasheet, specifications and performance data are constantly changing. Latest details can be obtained from the Electrium website.



Electrium Sales Limited, Walkmill Lane, Cannock WS11 0XE
01543 455000 www.electrium.co.uk info@electrium.co.uk