



- Screwless Plate
- Dual Voltage
- Satin Chrome Finish
- Black Interior

Product Specification Data		Revision Date: 15/10/2021
Product Standard/s	BS EN 61558-2-5	
Terminal Capacity L&N	4 x 1.0, 3 x 1.5 mm <sup>2</sup>	
Terminal Capacity E	4 x 1.0, 3 x 1.5 mm <sup>2</sup>	
Frequency	50 Hz	
Printing	Shavers Only, Shaver Symbol	
CE Conformity	Yes	
WEEE Symbol	Yes	
UKCA Conformity	Yes	
Assembly arrangement	Basic element With central cover plate	
Mounting method	Surface mounted (plaster)	
Nominal voltage low value	115 V	
Nominal voltage high value	230 V	
Material	Metal	
Material quality	Other	
Halogen free	Yes	
Surface protection	Other	
Surface finishing	Glossy	
Colour	Chrome	
Width of device	88 mm	
Height of device	148 mm	
With built-in installation box	No	
Min. depth of built-in installation box	55 mm	

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this datasheet, specifications and performance data are constantly changing. Latest details can be obtained from the Electrium website.