



The **ANSMANN 16340** 3.6V Li-Ion protected battery (RCR123A) with USB charging socket is extremely long lasting and can be recharged up to 2000 times even under tough operating conditions.

- Equivalent to **CR123A** – but rechargeable either with a lithium charger or through the micro USB
- Charge status LED on the positive pole of the battery
- With a very low self-discharge the battery keeps its charge for a long time, even when not used.
- The power to weight ratio is much better than other battery technologies (eg. NiCD/NiMH/PB), with Lithium being much lighter.
- Ideal in modern devices like LED torches, headlamps, e-cigarettes, laser pens, etc.
- High capacity of 850 mAh this is perfect for use in high power devices
- Can be used in a wide range of temperatures from -20°C to +60°C.
- The integrated safety board makes this battery slightly larger than the 16340 inside – 17350 (17x35mm approximately)

INFORMATION

Product name: Protected 16340 Li-Ion USB
Article number: 1300-0015
EAN-Code: 4013674161386
Product: 17x35x17mm/ 17g
Packing + Product: 86x23x123mm/ 26g
Packing unit: 10 (129x116x131mm) /305g

Available: Nov 2021
Custom tariff number: 85076000