





SLR-4400 DUAL POWER WORK LIGHT

- 4400 lumen 50W white COB LED, 6500k
- Dual Power rechargeable battery and mains powered
- Super tough IK07 aluminium & TPR construction
- Built-in aluminium heat sink
- 180° Vertical adjustable stand/handle
- Tripod & magnet mountable via hole in stand
- IP65 dust & water resistant
- Powerful 11.1v 5200mAh integrated li-ion battery
- **BATTERY** 11.1v 5200mAh Li-ion

WEIGHT 1150g

DIMENSIONS 225 x 220 x 70mm

- Battery level and charging indicators
- Mains 15V 1.5A multi-country charger/power lead included
- Quick 4 hour charge time
- Magnet attachment and tripods available to purchase separately

LUMEN 4400LM | RUNTIME 2-9H | BEAM 74M | IP RATING IP65/IK07

WWW.UNILITE.CO.UK #BUILT TOUGH