

## END OF LIFE NOTICE

**Product Category** : AC/DC Converters

**Issue Date** : 13 - FEB - 2022

**Effective Date** : 13 - FEB - 2022

**Reason For Change** : Due to low volume sales, manufacturer has decided to make the following parts as OBSOLETE.

**LTB Date** : N/A (Until Stock Exhaust)

**LTD Date** : N/A (Until Stock Exhaust)

**Change to Form Fit Function** : There is no change to Form, Fit or Function.

**Part Effected** : Below are the part numbers which are Affected.

END OF LIFE	REPLACEMENT-1	REPLACEMENT-2
A025N-5		
AEB100PS12	VES120PS12	VES90PS12
AEB100PS125	VES120PS12	VES90PS12
AEB100PS15	VES150PS48	
AEB100PS24	VES120PS24	VES90PS24
AEB100PS48	VES150PS48	
AEB36US05		
AEB36US09	AKM36US09C2	
AEB36US12	VET36US120C2-JA	
AEB36US13		
AEB36US15	VET36US150C2-JA	
AEB36US18	VET36US180C2-JA	
AEB36US24	VET36US240C2-JA	
AEB36US48		
AEB45US12	AKM45US12C2	VEC50US12
AEB45US15	VEC50US15	



# XP Power

AEB45US19	VEC50US19	
AEB45US24	VEC50US24	
AEB45US48	AKM45US48C2	
AED36US05		
AED36US09	AKM36US09C2	
AED36US12	VET36US120C2-JA	
AED36US15	VET36US150C2-JA	
AED36US18	VET36US180C2-JA	
AED36US24	VET36US240C2-JA	
AED36US48		
AED45US05		
AED45US12	VEC50US12	
AED45US15	VEC50US15	
AED45US18	VEC50US19	
AED45US24	VEC50US24	
AED45US48	AKM45US48	
AED70US12	VES90PS12	
AED70US15		
AED70US18		
AED70US19	VES120PS19	
AED70US24	VES90PS24	
AED70US48	VES90PS48	
AEH130PS05		
AEH130PS12	VES120PS12	
AEH130PS24	VES120PS24	
AEH130PS28		
AEH130PS48	VES150PS48	
AEH15US03		
AEH15US05		
AEH15US12	VET18US120C2-JA	
AEH15US15	VET18US150C2-JA	
AEH15US24	VET18US240C2-JA	
AEH45UM22		
AEH45UM28		
AEH45UM33		
AEH45US12	AKM45US12	VEC40US12
AEH45US24	AKM45US24	VEC40US24
AEH45US36		
AEH80UM31		



POWERING THE WORLD'S CRITICAL SYSTEMS



# XP Power

AEH80UM32		
AEH80US15	AKM90PS15	
AEH80US48	VES90PS48	
AEJ36US05		
AEJ36US09	AKM36US09C2	
AEJ36US12	AKM36US12C2	
AEJ36US15	AKM36US15C2	
AEJ36US18		
AEJ36US24	AKM36US24C2	
AEJ36US48		
AEK15US05		
AEK15US08		
AEK15US18	VET18US180C2-JA	
AEK15US24	AKM36US24C2	VET18US240C2-JA
AEK15US30		
AEK15US36		
AEK40US13		
AEK40US18	AKM45US18	
AEK60US15	ALM65US15	AKM65US15
AEK60US18	AKM65US18	
AEK60US24	ALM65US24	VEC65US24
AEL15US03		
AEL15US05		
AEL15US08		
AEL15US09	VET18US090C2-JA	
AEL15US12	VET18US120C2-JA	
AEL15US15	VET18US150C2-JA	
AEL15US18	VET18US180C2-JA	
AEL15US24	VET18US240C2-JA	
AEL15US30		
AEL15US36		
AEL15US48		
AEL20US05		
AEL20US05C2		
AEL20US12	VET24US120C2-JA	
AEL20US12C2	VET24US120C2-JA	
AEL20US15	VET24US150C2-JA	
AEL20US24	VET24US240C2-JA	
AEL20US24C2	VET24US240C2-JA	





# XP Power

AEL20US30		
AEL20US48		
AEL40US05		
AEL40US09		
AEL40US12	VEC40US12	
AEL40US18	VET36US180C2-JA	
AEL40US24	VEC40US24	
AEL40US36		
AEL40US48	AKM45US48	
AEL60US12	VEC65US12	
AEL60US18	AKM65US18	
AEL60US24	VEC65US24	
AEL60US30		
AEL60US48	AKM65US48	
AEL80US15	AKM90PS15	
AEL80US18		
AEL80US30		
AEL80US36		
AEL80US48	VES90PS48	
AEM60US05		
AEM60US12	AKM65US12C2	
AEM60US15		
AEM60US18	AKM65US18C2	
AEM60US19		
AEM60US24	AKM65US24C2	
AEM60US36		
AEM60US48	AKM65US48C2	
AFE220PS12		
AFE220PS19		
AFE220PS24		
AFE220PS48		
AFM120PS12	ALM120PS12	
AFM120PS15	ALM120PS15	
AFM120PS18	ALM120PS19	
AFM120PS24	ALM120PS24	
AFM120PS48	ALM150PS48	
AFM30US12C2		
AFM45US18C2	AKM45US18C2	
AFM45US24C2	AKM45US24C2	



POWERING THE WORLD'S CRITICAL SYSTEMS



# XP Power

AG50N-5		
AJM90PS12	AKM90PS12	
AJM90PS12C2	AKM90PS12	
AJM90PS18	AKM90PS19	
AJM90PS18C2	AKM90PS19	
AJM90PS19	AKM90PS19	
AJM90PS19C2	AKM90PS19	
AJM90PS24	AKM90PS24	
AJM90PS24C2	AKM90PS24	
AMM120PS12	ALM120PS12	
AMM120PS15	ALM120PS15	
AMM120PS18		
AMM120PS19	ALM120PS19	
AMM120PS20		
AMM120PS24	ALM120PS24	
AMM120PS30		
AMM120PS36		
AMM120PS48		
AMM150PS12	ALM150PS12	
AMM150PS15	ALM150PS12	
AMM150PS19	ALM150PS12	
AMM150PS24	ALM150PS12	
AMM150PS27		
AMM150PS48	ALM150PS12	
CU10-00		
CU10-09		
CU10-10		
CU10-12		
CU10-13		
CU10-14		
CU15-00		
CU15-09		
CU15-10		
CU15-12		
CU15-13		
CU15-14		
DNR120TS12		
DNR240TS48-I		
DNR480TS24-I		





# XP Power

DNR480TS48-I		
DNR960TS24-I		
DNR960TS48-I		
DSA150PS24	DSR120PS24	
DSA150PS48	DSR120PS48	
DSA240PS24	DSR240PS24	
DSA240PS48	DSR240PS48	
DSA480PS24	DNR480PS24-I	
DSA480PS48	DNR480PS48-I	
DSA-DP20		
DSF100-H		
DSF200LV-H		
DSF206-H		
DSF500-H		
ECP40UT03		
ECP60US05	ECS60US05	VCB60US05
ECP60UT01		
ECP60UT03		
EMA212PS12	GCS250PS12	
EMA212PS24	GCS250PS24	
EMA212PS48	GCS250PS48	
HCP650PS05		
HCP650PS12	HDS800PS12	
HCP650PS15	HDS800PS15	
HCP650PS24	HDS800PS24	
HCP650PS27	HDS800PS30	
HCP650PS48	HDS800PS48	
IA1209D		
IA4803D		
IA4803S		
IA4805D		
IA4805S		
IA4809D		
IA4809S		
IA4812D		
IA4812S		
IA4815D		
IA4815S		
IA4824D		



POWERING THE WORLD'S CRITICAL SYSTEMS



# XP Power

IA4824S		
IC0503DA-H		
IC0505DA		
IC0505DA-H		
IC0509DA		
IC0512DA		
IC0515DA		
IC1205DA		
IC1209DA		
IC1212DA		
IC1215DA		
ID0505S		
ID0505SA		
ID0509S		
ID0509SA		
ID0512S		
ID0512SA		
ID0515S		
ID0515SA		
ID1205S		
ID1205SA		
ID1209S		
ID1209SA		
ID1212S		
ID1212SA		
ID1215S		
ID1215SA		
IG0505S		
IG0505SA		
IG0509S		
IG0509SA		
IG0512S		
IG0512SA		
IG0515S		
IG0515SA		
IG1205S		
IG1205SA		
IG1209S		
IG1209SA		





# XP Power

IG1212S		
IG1212SA		
IG1215S		
IG1215SA		
IG2405S		
IG2405SA		
IG2409S		
IG2409SA		
IG2412S		
IG2412SA		
IG2415S		
IG2415SA		
IH4803D		
IH4803S		
IH4803SH		
IH4805D		
IH4805S		
IH4805SH		
IH4809D		
IH4809S		
IH4809SH		
IH4812D		
IH4812S		
IH4812SH		
IH4815D		
IH4815S		
IH4815SH		
IH4824D		
IH4824S		
IH4824SH		
IJ0505DA		
IJ0512DA		
IJ0515DA		
IJ1205DA		
IJ1212DA		
IJ1215DA		
IJ2405DA		
IJ2412DA		
IJ2415DA		







# XP Power

IK4803SA		
IK4805SA		
IK4812SA		
IK4815SA		
IK4824SA		
IL4803S		
IL4805S		
IL4809S		
IL4812S		
IL4815S		
IL4824S		
ISA0505		
ISA0505-H		
ISA0509	IAS0105D09	
ISA0509-H		
ISA0512		
ISA0512-H		
ISA0515	IAS0105D15	
ISA0515-H		
ISA0524	IAS0105D24	
ISA0524-H		
ISA1215-H		
ISA1224		
ISA1224-H		
ISE0503A-H	IES0105S03-H	
ISE0506A-H		
ISE0509A	IES0105S09	
ISE0509A-H		
ISE0512A-H		
ISE0515A-H		
ISE0524A-H		
ISE1215A-H		
ISE1224A-H		
ISF0303A-H	ISD0103S3V3	
ISF0303A-X	ISD0103S3V3	
ISF0305A-H	ISD0103S05	
ISF0305A-X	ISD0103S05	
ISF0503A	IES0105S03	
ISF0503A-H	IES0105S03-H	





# XP Power

ISF0503A-X	IES0105S03	
ISF0505	IAS0105D05	
ISF0505A		
ISF0505A-H	IES0105S05-H	
ISF0505A-X	IFS0105S05	
ISF0505-H		
ISF0505-X	IAS0105D05	
ISF0509	IAS0105D09	
ISF0509A		
ISF0509A-H		
ISF0509A-X	IAS0105D09	
ISF0509-H		
ISF0509-X	IAS0105D09	
ISF0512	IAS0105D12	
ISF0512A	IFS0105S12	
ISF0512A-H		
ISF0512A-X	IFS0105S12	
ISF0512-H		
ISF0512-X	IAS0105D12	
ISF0515	IAS0105D15	
ISF0515A	IES0105S15	
ISF0515A-H		
ISF0515A-X	IES0105S15	
ISF0515-H		
ISF0515-X	IAS0105D15	
ISF1205		
ISF1205A		
ISF1205A-H		
ISF1205A-X		
ISF1205-H		
ISF1205-X		
ISF1209		
ISF1209A		
ISF1209A-H		
ISF1209A-X		
ISF1209-H		
ISF1209-X		
ISF1212		
ISF1212A-H		





# XP Power

ISF1212A-X		
ISF1212-H		
ISF1212-X		
ISF1215		
ISF1215A		
ISF1215A-H		
ISF1215A-X		
ISF1215-H		
ISF1215-X		
ISF2403A		
ISF2403A-X		
ISF2405		
ISF2405A-X		
ISF2405-X		
ISF2409		
ISF2409A		
ISF2409A-X		
ISF2412		
ISF2412A		
ISF2412A-H		
ISF2412A-X		
ISF2412-H		
ISF2412-X		
ISF2415		
ISF2415A		
ISF2415A-X		
ISF2415-X		
ISF2424		
ISF2424A		
ISF2424A-X		
ISF2424-X		
ISG0505A		
ISG0505A-X		
ISG0512A		
ISG0512A-X		
ISG0515A		
ISG0515A-X		
ISG1205A		
ISG1205A-X		





# XP Power

ISG1212A		
ISG1212A-X		
ISG1215A		
ISG1215A-X		
ISH1212A-H	ISV0212S12	
ISH1215A-H	ISV0212S15	
ISJ0505A		
ISJ0505A-H		
ISJ0509A		
ISJ0512A		
ISJ0515A		
ISJ1205A		
ISJ1209A		
ISJ1212A		
ISJ1215A		
ISK0509A	IES0105S09	
ISK0515A	IES0105S15	
ISK1209A	IES0112S09	
ISL2403A		
ISL2405		
ISL2405A		
ISL2409A		
ISL2412		
ISL2412A		
ISL2415		
ISL2415A		
ISL4803A		
ISL4805		
ISL4805A		
ISL4809A		
ISL4812		
ISL4812A		
ISL4815		
ISL4815A		
ISP1203A		
ISP1205		
ISP1205A		
ISP1209A		
ISP1212		





# XP Power

ISP1212A		
ISP1215		
ISP1215A		
ISP2403A		
ISP2405		
ISP2405A		
ISP2409A		
ISP2412		
ISP2412A		
ISP2415		
ISP2415A		
ISQ0505A		
ISQ0512A		
ISQ0515A		
ISQ1205A		
ISQ1212A		
ISQ1215A		
ISQ2405A		
ISQ2412A		
ISQ2415A		
ISR1205A		
ISR1212A		
ISR1215A		
ISR2405A		
ISR2412A		
ISR2415A		
ISR4805A		
ISR4812A		
ISR4815A		
IST0505A	ISH0505A	
IST0505A-X	ISH0505A	
IST0512A	ISH0512A	
IST0512A-X	ISH0512A	
IST0515A	ISH0515A	
IST0515A-X	ISH0515A	
IST1205A	ISH1205A	
IST1205A-X	ISH1205A	
IST1212A	ISH1212A	
IST1212A-X	ISH1212A	



POWERING THE WORLD'S CRITICAL SYSTEMS



# XP Power

IST1215A	ISH1215A	
IST1215A-X	ISH1215A	
IST2405A	ISH2405A	
IST2405A-X	ISH2405A	
IST2412A	ISH2412A	
IST2412A-X	ISH2412A	
IST2415A	ISH2415A	
IST2415A-X	ISH2415A	
ISW0503A		
ISW0503A-H		
ISW0505A		
ISW0505A-H		
ISW0512A		
ISW0512A-H		
ISW0515A		
ISW0515A-H		
ISW1205A		
ISW1205A-H		
ISW1212A		
ISW1212A-H		
ISW1215A		
ISW2405A		
ISW2405A-H		
ISW2412A		
ISW2412A-H		
IV4803S		
IV4803SA		
IV4805S		
IV4805SA		
IV4809S		
IV4809SA		
IV4812S		
IV4812SA		
IV4815DA		
IV4815S		
IV4815SA		
IV4824S		
IV4824SA		
JPS130PS05-M		





# XP Power

JPS250 F/CVR		
JPS250 F/CVR 24		
JPS250 F/CVR 5		
JPS250PQ41		
JPS250PQ46		
JPS250PQ47		
JPS250PQ48		
JPS250PS05		
JPS250PS05C		
JPS250PS12		
JPS250PS12C		
JPS250PS15		
JPS250PS15C		
JPS250PS24		
JPS250PS24C		
JPS250PS48		
JPS250PS48C		
JPS350 F/CVR		
JPS350 F/CVR 5		
JPS350PS05		
JPS350PS05C		
JPS350PS12		
JPS350PS12C		
JPS350PS15		
JPS350PS15C		
JPS350PS24		
JPS350PS24C		
JPS350PS48		
JPS350PS48C		
LCL150PS12	GCS180PS12	
LCL150PS15	GCS180PS15	
LCL150PS24	GCS180PS24	
LCL150PS48	GCS180PS48	
LCL300PS12	SMP350PS12	
LCL300PS13		
LCL300PS15	SMP350PS15	
LCL300PS24	SMP350PS24	
LCL300PS27	SMP350PS28	
LCL300PS48	SMP350PS48	





# XP Power

LCL500PS12	GCU500PS12-EF	
LCL500PS15	GCU500PS15-EF	
LCL500PS24	GCU500PS24-EF	
LCL500PS48	GCU500PS48-EF	
LDU0516S300		
LDU0516S350		
LDU0716S500		
LDU0830S300		
LDU0830S350		
LDU0830S350-W		
LDU0830S350-WD		
LDU1416S1000		
LDU1416S600		
LDU1416S700		
LDU2030S500		
LDU2030S600		
LDU2030S700		
LDU2430S1000		
LDU2430S1000-WD		
LDU2430S500		
LDU2430S500-WD		
LDU2430S600		
LDU2430S700		
LDU2430S700-WD		
LDU4860S1000		
LDU4860S1000-WD		
LDU4860S150		
LDU4860S150-WD		
LDU4860S250		
LDU4860S250-W		
LDU4860S250-WD		
LDU4860S300		
LDU4860S350		
LDU4860S350-WD		
LDU4860S500		
LDU4860S500-WD		
LDU4860S700		
LDU4860S700-WD		
LDU5660S1000		







# XP Power

LDU5660S1000-WD		
LDU5660S300		
LDU5660S300-WD		
LDU5660S350		
LDU5660S350-WD		
LDU5660S500		
LDU5660S500-WD		
LDU5660S600		
LDU5660S600-WD		
LDU5660S700		
LDU5660S700-WD		
PCM50UD02		
PCM50UD03		
PCM50US05		
PCM50US07		
PCM50US09		
PCM50US15	AKM65US15	AKM45US15
PCM50US18	AKM65US18	AKM45US18
PCM50US28		
PCM50US2V5		
PCM50US36		
PCM50US3V3		
PCM50US48	AKM65US48	
PCM50UT03		
PCM50UT07		
SDH400PD1224		
SDH400PS12	CCL400PS12	
SDH400PS24	CCL400PS24	
SDH400PS48	CCL400PS48	
SDS120PD02B-C		
SDS120PD02B-CP		
SDS120PD02B-L		
SDS120PD04-P		
SDS120PS05B		
SDS120PS05B-L		
SDS120PS07B		
SDS120PS09B		
SDS120PS09B-C		
SDS120PS12		





# XP Power

SDS120PS15B		
SDS120PS24B-L		
SDS120PS24B-P		
SDS120PS28		
SDS120PS36B		
SDS120PS48B		
SDS120PT00B		
SDS120PT08B-L		
SDS120PT09B		
SDS120PT09B-C		
SDS120PT09B-L		
SDS120PT10B-C		
SDS150PS09B		
SDS150PS12B		
SDS150PS12B-L		
SDS150PS15B		
SDS150PS18B		
SDS150PS18B-C		
SDS150PS24B-L		
SDS150PS24B-P		
SDS150PS24-L		
SDS150PS30B		
SDS150PS36B-CL		
SDS150PS36B-L		
SDS150PS36-P		
SDS150PS48		
SDS180PS12B	GCS250PS12	UCP225PS12
SDS180PS24B	GCS250PS24	UCP225PS24
SDS180PS48B	GCS250PS48	UCP225PS48
SDS60 COVER KIT		
SDS60UD01		
SDS60UD01-B		
SDS60UQ14		
SDS60US03		
SDS60US05		
SDS60US07		
SDS60US09		
SDS60US15B		
SDS60US19		





# XP Power

SDS60US24-B		
SDS60US30		
SDS60US36		
SDS60US48		
SDS60US48-B		
SDS60UT00		
SDS60UT03		
SDS60UT05-C		
SDS60UT09		
SDU150PS24		
TR2005S1V2		
TR2005S1V5		
TR2005S1V8		
TR2005S2V5		
TR2024S05		
TR2024S09		
TR2024S12		
TR2024S15		
TR2024S1V2		
TR2024S1V5		
TR2024S1V8		
TR2024S2V5		
TR2024S3V3		
TR2024S6V5		
VCP15US12-E	VCE20US12	
VCP15US15-E	VCE20US15	
VCP24US05	VCE20US05	
VCP24US05-E	VCE20US05	
VCP24US12	VCE20US12	VCE40US12
VCP24US12-E	VCE20US12	VCE40US12
VCP24US15	VCE20US15	VCE40US15
VCP24US15-E	VCE20US15	
VCP24US24	VCE20US24	VCE40US24
VCP24US24-E	VCE20US24	VCE40US24
VCS100US15		
VCS100US48		
VCT40US05	VCB60US05	
VCT60US12	VCB60US12	
VCT60US15	VCB60US15	





# XP Power

VCT60US24	VCB60US24	
VEF50US12	VEC50US12	
VEF50US15	VEC50US15	
VEF50US19	VEC50US19	
VEF50US24	VEC50US24	
VEF65US12	VEC65US12	
VEF65US19	VEC65US19	
VEF65US24	VEC65US24	
VEH120PS12	VES120PS12	
VEH120PS19	VES120PS19	
VEH120PS24	VES120PS24	
VEH150PS12		
VEH150PS19		
VEH150PS24		
VEH20US05		
VEH20US05C2		
VEH20US12	VET24US120C2-JA	
VEH20US12C2	VET24US120C2-JA	
VEH20US12-L6	VET24US120C2-JA	
VEH20US15	VET24US150C2-JA	
VEH20US15C2	VET24US150C2-JA	
VEH20US18	VET24US180C2-JA	
VEH20US18C2	VET24US180C2-JA	
VEH20US24	VET24US240C2-JA	
VEH20US24C2	VET24US240C2-JA	
VEH20US48		
VEH20US48C2		
VEH40US05		
VEH40US05C2		
VEH40US12	VEC40US12	
VEH40US12C2	VET36US120C2-JA	
VEH40US15	VEC40US15	
VEH40US15C2	VET36US150C2-JA	
VEH40US18	AKM45US18	
VEH40US18C2	VET36US180C2-JA	
VEH40US24	VEC40US24	
VEH40US24C2	VET36US240C2-JA	
VEH40US48	AKM45US48	
VEH40US48C2	AKM45US48C2	





# XP Power

VEH60US12	VEC65US12	
VEH60US15		
VEH60US24	VEC65US24	
VEH90PS12	VES90PS12	
VEH90PS19	VES90PS19	
VEH90PS24	VES90PS24	
VEP08US05	VER12US050-JA	
VEP08US09	VER12US090-JA	
VEP08US12	VER12US120-JA	VER18US120-JA
VEP15US05	VER12US050-JA	
VEP15US09	VER12US090-JA	VER18US090-JA
VEP15US12	VER12US120-JA	VER18US120-JA
VEP15US24	VER18US240-JA	
VEP36US09		
VEP36US12		
VEP36US15		
VEP36US24		
VES150PS12		
VES150PS15		
VES150PS19		
VES150PS24		
VFT80US05		
VFT80US12	LCE80PS12	ECS100US12
VFT80US15	LCE80PS15	ECS100US15
VFT80US24	LCE80PS24	ECS100US24
DLE15PS1250-A		
DLE15PS12-V		
DLE15PS24-V		
DLE15PS350-A		
DLE15PS500-A		
DLE15PS700-A		
DLE25PS12		
DLE25PS24		
DLE25PS36		
DLE25PS48		
DLE25PS57		
DLE35PS12		
DLE35PS24		
DLE35PS36		





# XP Power

DLE35PS48		
DLE35PS57		
DLE45PS24		
DLE45PS36		
DLE45PS48		
DLE45PS57		
DLE60PS12		
DLE60PS24		
DLE60PS36		
DLE60PS48		
DLE60PS57		
DLG100PS12		
DLG100PS1400-A		
DLG100PS24		
DLG100PS36		
DLG100PS48		
DLG100PS700-A		
DLG100PS800-A		
DLG150PS1050-A		
DLG150PS12		
DLG150PS1400-A		
DLG150PS24		
DLG150PS350-A		
DLG150PS36		
DLG150PS48		
DLG150PS530-A		
DLG150PS700-A		
DLG50PS12		
DLG50PS24		
DLG50PS36		
DLG50PS48		
DLG70PS700-A		
DLG75PS12		
DLG75PS24		
DLG75PS36		
DLG75PS48		

