

PROFESSIONAL DEGAUSSING COIL

Eliminates magnetic fields in CRT TV picture tubes and Computer Monitors (must be "on")

Supplied with a momentary contact switch that permits de-energizing of the coil without unplugging the unit. UL approved UL-LISTED 23U2. Safe to use.

FEATURES:

- OPERATING VOLTAGE: 117 Vac, 60 Hertz ONLY
- POWER CONSUMPTION: 325 VA, 2.8 Amps
- 8 Ft., 2 Cond. SPT-2 Cord, with POLARIZED Plug
- 250 Turns of 24 AWG Enameled Magnet Wire
- INTERMITTENT DUTY CYCLE: 1 Minute "ON", 30 Minutes "OFF" to Cool
- 13" Outside Dia., 11-1/4" Inside Dia. x 1" Thick Coil, FLAME RETARDANT ABS High Impact Plastic Case Housing
- Momentary (Spring Return) Push Button Heavy Duty On/Off Switch
- WEIGHT: 2-1/4 Lbs.

Product Availability:

PART No.	DESCRIPTION	SIZE
9317	Degaussing Coil	13"



N.S.N. 5950-01-046-7345
UPC: 010151150837
HTS: 8205.59.5560

CoO: USA

Keep away from any form of magnetic media.
This unit will erase magnetic media.

Warning: Do not use if it is hot to the touch.

NOTE: This product must not be operated for more than one minute continuously. After using for up to one minute do not operate for thirty minutes to allow unit to cool.

To use, plug unit into receptacle near TV or computer monitor (must be "on") to be degaussed. Move as far as possible from set (minimum of 6 ft.) and press switch. Holding the coil so that the plane of the coil is parallel to the front of the tube, move coil in a circular motion while approaching the face of the screen. Continue the circular motions passing over the complete surface of the screen until you are within inches of the screen. While continuing this motion move slowly away from the screen until you are as far away as possible, then release the switch.



PART No: **9317**