



Technical Hotline
+44 (0)1268 563720

Boxes

PVC Boxes

19MM
SURFACE



2120WHI
FOR 1, 2 AND 3 GANG
PLATESWITCHES

10

With earth terminal
DIMENSIONS
87 x 87mm
FIXING CENTRES
60.3mm

Knockouts 'Cut-out' provided
in top and bottom for 16mm
oval PVC conduit. 20mm round
'push-out' type knockout in base
for cable entry. Fixing holes are
also provided for mounting to
wall or over BS 4568-2 small
circular boxes.

BS 5733:2010

32MM
SURFACE



2180WHI
1 GANG
2181WHI
1 GANG

10

10

DIMENSIONS
87 x 87mm
FIXING CENTRES
60.3mm

KNOCKOUTS

2180: One 'push-out' for 20mm
oval conduit in top, one 'cut-out'
for 20mm or 25mm oval conduit
and one 20mm round 'push-out'
in the base.

2181: One 'push-out' for 20mm
round conduit in top and one 20mm
round 'push-out' in base.
BS 5733:2010



2182WHI
2 GANG
2183WHI
2 GANG

5

5

DIMENSIONS
87 x 148mm
FIXING CENTRES
120.6mm

KNOCKOUTS

2182: Two 'push-outs' for 20mm
oval conduit in top, two 'cut-outs'
for 20mm or 25mm oval conduit
and one 20mm round 'push-out'
in base

2183: One 'push-out' for 20mm
round conduit in top and one
20mm round 'push-out' in base.
BS 5733:2010



K2181WHI
FOR 1 GANG LOGIC PLUS™ POWER ACCESSORIES
K2183WHI
FOR 2 GANG LOGIC PLUS™ POWER ACCESSORIES
K2185WHI
FOR 3 GANG LOGIC PLUS™ POWER ACCESSORIES

10

5

5

KNOCKOUTS

K2181: One 'cut-out' for 20mm round conduit in top
face, one 'cut-out' for 20mm or 25mm oval conduit
in lower face and one 20mm round 'push-out' in
the base.

K2183 and K2185: One 'cut-out' for 20mm round
conduit in top face, two 'cut-outs' for 20mm or
25mm oval conduit in lower face and one 20mm
round 'push-out' in the base. Both boxes are suitable
for fitting over 1 gang and 2 gang BS 4662 flush
steel boxes respectively.

DIMENSIONS

1 gang: 87 x 87mm
2 gang: 87 x 148mm
3 gang: 87 x 208mm

FIXING CENTRES

1 gang: 60.3mm
2 gang: 120.6mm
3 gang: 180.9mm
BS 4662:2006
where applicable

Moulded Boxes

ARCHITRAVE
SURFACE



K2151WHI
1 GANG
ARCHITRAVE BOX
K2152WHI
2 GANG
ARCHITRAVE BOX

10

5

Earth terminal fitted in base of
boxes.

DIMENSIONS
1 gang: 87 x 33 x 16mm
2 gang: 148 x 33 x 16mm

FIXING CENTRES
1 gang: 60.3mm
2 gang: 120.6mm
BS 5733:2010

16MM
SURFACE



K2160WHI
FOR 1, 2 AND
3 GANG LOGIC PLUS™ PLATESWITCHES
K2161WHI
FOR 4 AND 6 GANG
LOGIC PLUS™
PLATESWITCHES

10

5

Earth terminal fitted in base of boxes.
Knockouts provided in sides and bases.

DIMENSIONS
1 gang: 87 x 87mm
2 gang: 87 x 148mm

FIXING CENTRES
1 gang: 60.3mm
2 gang: 120.6mm
BS 5733:2010

30MM
SURFACE



K2140WHI
FOR 1 GANG
LOGIC PLUS™
POWER ACCESSORIES
K2142WHI
FOR 2 GANG
LOGIC PLUS™
POWER ACCESSORIES

10

5

Knockouts in base and sides for
cable entry
K2142 and K2153 are suitable
for fitting over 1 gang and
2 gang BS 4662 flush steel boxes
respectively

K2153WHI
FOR 3 GANG
LOGIC PLUS™
POWER ACCESSORIES

5

DIMENSIONS
1 gang: 87 x 87mm
2 gang: 87 x 148mm
3 gang: 87 x 208mm

FIXING CENTRES
1 gang: 60.3mm
2 gang: 120.6mm
3 gang: 180.9mm
BS 5733:2010