

CEE-Connectors and -Sockets

Shark Connector

- with screw terminals
- with Shark cable gland

IP44



Ampere

Poles

110V~
50/60Hz
4h

230V~
50/60Hz
3p=6h
4p+5p=9h

400V~
50/60Hz
3p=9h
4p+5p=6h

Cat.No.

Cat.No.

Cat.No.

16	3	213-4	213-6	213-9
16	4	214-4	214-9	214-6
16	5	215-4	215-9	215-6
32	3	223-4	223-6	223-9
32	4	224-4	224-9	224-6
32	5	225-4	225-9	225-6

Turbo Shark Connector

- screwless connection technology
- with Shark cable gland

IP44



16	3	213-4TT	213-6TT	213-9TT
16	4	214-4TT	214-9TT	214-6TT
16	5	215-4TT	215-9TT	215-6TT
32	3	223-4TT	223-6TT	223-9TT
32	4	224-4TT	224-9TT	224-6TT
32	5	225-4TT	225-9TT	225-6TT

Shark Connector

- with screw terminals
- with Shark cable gland

IP66/67



16	3	2132-4	2132-6	2132-9
16	4	2142-4	2142-9	2142-6
16	5	2152-4	2152-9	2152-6
32	3	2232-4	2232-6	2232-9
32	4	2242-4	2242-9	2242-6
32	5	2252-4	2252-9	2252-6

Turbo Shark Connector

- screwless connection technology
- with Shark cable gland

IP66/67



16	3	2132-4TT	2132-6TT	2132-9TT
16	4	2142-4TT	2142-9TT	2142-6TT
16	5	2152-4TT	2152-9TT	2152-6TT
32	3	2232-4TT	2232-6TT	2232-9TT
32	4	2242-4TT	2242-9TT	2242-6TT
32	5	2252-4TT	2252-9TT	2252-6TT

Power Twist Connector

- contact frame with screws
- with lamellar contact
- with Twist cable gland

IP66/67



63	3	233-4	233-6	233-9
63	4	234-4	234-9	234-6
63	5	235-4	235-9	235-6
125	3	243-4	243-6	243-9
125	4	244-4	244-9	244-6
125	5	245-4	245-9	245-6

Wall socket

- with screw terminals
- top (M25) or rear entry

IP44



16	3	113-4	113-6	113-9
16	4	114-4	114-9	114-6
16	5	115-4	115-9	115-6
32	3	123-4	123-6	123-9
32	4	124-4	124-9	124-6
32	5	125-4	125-9	125-6

Turbo Twist Wall socket

- screwless connection technology
- top (M25) or rear entry

IP44



16	3	113-4TT	113-6TT	113-9TT
16	4	114-4TT	114-9TT	114-6TT
16	5	115-4TT	115-9TT	115-6TT
32	3	123-4TT	123-6TT	123-9TT
32	4	124-4TT	124-9TT	124-6TT
32	5	125-4TT	125-9TT	125-6TT

Wall socket

- with screw terminals
- top (M25) or rear entry

IP67



16	3	1132-4	1132-6	1132-9
16	4	1142-4	1142-9	1142-6
16	5	1152-4	1152-9	1152-6
32	3	1232-4	1232-6	1232-9
32	4	1242-4	1242-9	1242-6
32	5	1252-4	1252-9	1252-6