

230V~

50/60Hz
3p=6h
4p+5p=9h

400V~

50/60Hz
3p=9h
4p+5p=6h

Ampere

Poles

Cat.No.

Cat.No.

Event technology

16	3	013-6x	
16	4		014-6x
16	5		015-6x
32	3	023-6x	
32	4		024-6x
32	5		025-6x

Shark Plug

- with screw terminals
- to order screwless connection technology please add "TT" e.g. 013-6TTx

IP44



Solid rubber plug

- with screwless cable gland
- dual-point earthing system
- insert: rubber

IP44



05622-ss

63	3	033-6xs	
63	4		034-6xs
63	5		035-6xs
125	3	043-6xs	
125	4		044-6xs
125	5		045-6xs

Power Twist Plug

- Contact frame with screws

IP66/67



Solid rubber connector

- with screwless cable gland
- national
- with hinged lid
- insert: rubber

IP44



25622-ss

16	3	613-6x	
16	4		614-6x
16	5		615-6x
32	3	623-6x	
32	4		624-6x
32	5		625-6x

Flanged plug straight

- with screw terminals
- to order screwless connection technology please add "TT" e.g. 613-6TTx

IP44



3-way connector - solid rubber

- with screwless cable gland
- national
- with hinged lid
- insert: rubber

IP44



253622-sxs

16	3	213-6x	
16	4		214-6x
16	5		215-6x
32	3	223-6x	
32	4		224-6x
32	5		225-6x

Shark Connector

- with screw terminals
- to order screwless connection technology please add "TT" e.g. 213-6TTx

IP44



T-Connect

- Equipment:
1 CEE-plug 16A 3p 6h
1 CEE-socket 16A 3p 6h
1 cable entry

IP44 (IP67 available)
other versions on request



94325000

63	3	233-6xs	
63	4		234-6xs
63	5		235-6xs
125	3	243-6xs	
125	4		244-6xs
125	5		245-6xs

Power Twist Connector

- Contact frame with screws

IP66/67



Wall distribution boxes

- many designs available on request
- solid rubber

IP54



16	3	313-6x	
16	4		314-6x
16	5		315-6x
32	3	323-6x	
32	4		324-6x
32	5		325-6x

Flanged socket straight

- with screw terminals
- to order screwless connection technology please add "TT" e.g. 313-6TTx

IP44



Mobile distribution boxes

- many designs available on request
- solid rubber

IP44



250V~

50/60Hz

16	3	1050-0ss	
16	3	1050-0ssw	with sealing bulge

Socket outlet (DIN 49440)

- flange 50x50mm
- fixing center 38x38mm
- screwed contact
- available also with Belg./French and British system

IP54



Hinged windows

- available in different dimensions

IP67, IP54

