CONSTANT VOLTAGE LED DRIVER 24VDC 60WATT



POWERPAX: LED-DR-24V-60-SLIM

Features

- Input Voltage 200-240vac
- IP20 Rated
- Class II
- Compact Plastic Low Profile enclosure
- 1 Year Warranty



Description:

The Range of 60watt Constant Voltage LED Drivers are housed in a compact light weight high quality IP20 plastic enclosure with covered input & output terminals suitable for general Indoor LED applications

Specification	
Part Number	LED-DR-24V-60W-SLIM
Output Voltage Rating	24+/-5vdc
Output Current Range	2.5A
Rated Power	60 Watt
Dimensions	304.6 x 30 x 16.7mm
Input Voltage Range	200-240VAC
Input Voltage Frequency	50-60Hz
Inrush Current	<75A
input power	<75W
Efficiency	≥88%
Power Consumption Without Load	<0.5W
Overload Protection	Ta, input 0.94-1.06 times rated voltage, output 2 times rated load
Short Circuit Protection	Ta, input 0.94-1.06 times rated voltage, output short circuit for 1 hour
Automatically Restart	Ta, overload, short, over temperature protection retreat
Working Temperature	-20°C ~+45 °C
Relative Humidity	45%~85%
MTBF	30000hr
EMC emission	EN55015
EMC Immunity	EN61547
Safety Standards	IEC61347-1, IEC61347-2-13(with light IEC60598)

POWERPAX

CONSTANT VOLTAGE LED DRIVER 24VDC 60WATT



POWERPAX: LED-DR-24V-60-SLIM

Diagrams

