



Feature



- Made from impact resistant material that provides an IP54 seal
- Multiple cable access points for ease of use
- EP1GNB incorporates an LED indicator
- IP54 switches and sockets available
- All switches and sockets have a 13 amp rating
- Maximum load 3120 watts

Description	Product Code
IP54 Single UK socket	EP13SB
IP54 1 Gang 2 Way Switch	EP1G2B
IP54 1 Gang 2 Pole Switch	EP1G2P
IP54 1 Gang 2 Way Switch with LED Indicator	EP1GNB
IP54 13A Double UK Socket	EP213B
IP54 2 Gang 1 Way Switch	EP2G1B



Feature



- Sockets incorporate easy to open and close clip mechanism with extra locking mount
- Long lasting IP66 seal to withstand strong jets of water even when in use
- Switches have built in moulded multiple cable access points for convenience and a more robust seal
- 10, 20 and 13 amp ratings
- E6RDSK-N includes RCD protection to prevent against electrocution
- E61MTB-N has an inbuilt 24 hour timer
- 10A maximum load 2400 watts
- 13A Maximum load 3120 watts
- IP66

Description	Amp Rating	Product Code
Twin socket	13A	E613DB-N
Single socket	13A	E613SB-N
1 Gang 2 Way Switch - Neon	10A	E61G2B-N
1 Gang 2 Pole Switch - Neon	20A	E61G2P-N
Single socket with 24 hour timer	13A	E61MTB-N
2 Gang 2 Way Switch	10A	E62G2B-N
RCD Protected Single Socket	13A	E6RDSK-N
RF controlled single socket	13A	E6RFSB-N
RF controlled socket connection unit	13A	E6RFSP-N