

PHILIPS

Ledinaire



Trusted



Reliable



Great value

**REAL
PROs**
**REAL
QUALITY**



5
Year
Warranty

The one choice for every wall

Philips LED Ledinaire wall-mount

Now there's a Philips LED Ledinaire wall-mount to suit every application. This robust range continues to set the high quality standards you expect from our Ledinaire off-the-shelf luminaires. But it also features an optional motion detector to reduce energy consumption by up to 25%. So you now have a wider choice of reliable, hard-working LED solutions that deliver exactly what they promise. Perfect for replacing or upgrading existing wall-mounted fixtures in both indoor and outdoor applications.

Your benefits:

- ✓ Ideal for retrofitting applications (electrical Class II).
- ✓ Typical lifespan of 50,000 hours, efficacy to 100 lm/W.
- ✓ Optional motion and daylight detection unit with dipswitch for up to 25% dimming.
- ✓ BESA fixings and side entry
- ✓ Housing rated to IP65, IK08
- ✓ Emergency options available
- ✓ UV resistant

Application areas:

- ✓ Residential
- ✓ Public buildings
- ✓ Offices
- ✓ Healthcare facilities
- ✓ Parking garages
- ✓ Outdoor
- ✓ Stairwells
- ✓ Corridors






Supplied with tamper-proof screws




UV-resistant for outdoor use



Optional motion and day-light detection unit

Dimensions



Order information

Ledinaire wall-mounted



Description	Order code	Lumen	Efficacy	Colour temp	IP	Emergency
WL070V LED11S/840 PSU II WH UKI	911401855782	1100	Up to 100	4000	IP65 / IK08	
WL070V LED17S/840 PSU II WH UKI	911401855882	1700	Up to 100	4000	IP65 / IK08	
WL070V LED17S/840 PSU MDU II WH UKI	911401855982	1700	Up to 90	4000	IP65 / IK08	
WL070V LED11S/840 PSU II WH UKI ELB3	919313000019	1100	Up to 100	4000	IP65 / IK08	✓
WL070V LED17S/840 PSU II WH UKI ELB3	919313000020	1700	Up to 100	4000	IP65 / IK08	✓
WL070V LED17S/840 PSU MDU II WH UKI ELB3	919313000021	1700	Up to 90	4000	IP65 / IK08	✓

