



- Fully Rated to 13A
- Double Pole Switching
- Safety Shutter System

#### Product Specification Data

Revision Date: 15/10/2021

Product Standard/s	BS 1363-2
Terminal Capacity L&N	3 x 1.5, 3 x 2.5, 2 x 4.0 mm <sup>2</sup>
Terminal Capacity E	3 x 1.5, 3 x 2.5, 2 x 4.0 mm <sup>2</sup>
Frequency	50 Hz
LRV Value	73
CE Conformity	Yes
WEEE Symbol	Yes
G Mark	Yes
UKCA Conformity	Yes
Model	British Standard
Protective contact	No
Protective earth pin round	No
Number of active Pins (round)	0
Number of active Pins (flat)	3
With signal lamp	No
With built-in USB power supply	No
Number of units	1
Number of modules (module system)	0
Number of socket outlets switchable	2
Number of phases	2
Imprint/indication	Other
Connection type	Screwed terminal
With hinged lid	No
With child-protection	Yes
Label space/information surface	Yes
Colour	White
Lockable	No
Insulated mounting	Yes
With function lighting	No

Fault current protection	No
Special power supply	No special power supply
Mounting method	Surface mounted (plaster)
Type of fastening	Mounting With screw
Material	Plastic
Material quality	Other
Halogen free	Yes
Surface protection	Other
Surface finishing	Glossy
Antibacterial treatment	No
With on/off switch	Yes
Nominal current	13 A
Nominal voltage	250 V
Suitable for degree of protection (IP)	IP2X
Impact strength	IK02
Width of device	145 mm
Height of device	85 mm
Depth of device	31 mm
Min. depth of built-in installation box	25 mm

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this datasheet, specifications and performance data are constantly changing. Latest details can be obtained from the Electrium website.