



- Push On/Off
- Screwcap Covers

Product Specification Data

Revision Date: 15/10/2021

Product Standard/s	BS EN 60669-2-1
Terminal Capacity L&N	2 x 1.0, 1 x 2.5 mm ²
Frequency	50 Hz
LRV Value	73
CE Conformity	Yes
WEEE Symbol	Yes
UKCA Conformity	Yes
Wiring system	Two-way switch
Method of operation	Turn button
Assembly arrangement	Basic element
Number of modules (module system)	0
Push button switch	Yes
Number of rockers	2
Mounting method	Flush mounted (plaster)
Type of fastening	Screw mounting
With mounting plate	Yes
Material	Plastic
Material quality	Other
Halogen free	Yes
Surface protection	Other
Surface finishing	Glossy
Colour	White
Illumination	No
Function lighting	Other
Type of lighting	Incandescent lamp
Suitable for degree of protection (IP)	IP2X
Nominal voltage	250 V
Rated current	1.6 A
Connection type	Screwed terminal

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this datasheet, specifications and performance data are constantly changing. Latest details can be obtained from the Electrium website.

Product Specification Data (cont)		Revision Date: 15/10/2021
Width of device	86 mm	
Height of device	86 mm	
Min. depth of built-in installation box	35 mm	

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this datasheet, specifications and performance data are constantly changing. Latest details can be obtained from the Electrium website.



Electrium Sales Limited, Walkmill Lane, Cannock WS11 0XE
01543 455000 www.electrium.co.uk info@electrium.co.uk