


Product Specification

16 GB Neon USB 3.0



Neon USB 3.0 Flash Drive combines an eye-catching fluorescent casing with a SuperSpeed data transfer rate.

- Available in fluorescent Orange, Blue, Pink and Yellow
- USB 3.0 SuperSpeed
- Read speed up to 110MB/s*, and a Write speed up to 10 MB/s*
- PC and Mac compatible
- 2 year warranty

SKU	INFD16GBNEONB3.0
EAN	5055288418820

	Width (mm)	Depth (mm)	Height (mm)	Weight (g)
Product	18	8	54	8
Packaging	105	13	170	20

Capacity (GB)	16 GB
Read speed (MB per second)	110
Write speed (MB per second)	10
Security algorithms	N
Compatible operating systems	Windows Vista, 7, 8.1 and 10 Mac OS 09 and above Linux v2.4.0 and above

Key ring (Y/N)	N
Device interface	USB Type-A
USB housing	Cap
Product colour	Blue
Housing material	Plastic
Operating temperature (T-T) (degrees Celcius)	0 - 70
Package type	Blister
Certification	CE, REACH