

GFR281

56-in-1 Memory Card Reader/Writer



IOGEAR's newest Universal Memory Bank, 56-in-1 Memory Card Reader/Writer, is an ideal solution for hi-speed, bi-directional image and data file transfer between your computer and multimedia devices. Images and data can be downloaded directly from your memory cards*. It works with all major memory card formats and supports high capacity: CompactFlash/Micro Drive, SD/SDHC/Mini SD/MMC, Olympus and Fuji Film flash memory, T-Flash/microSD/ microSDHC, Memory Stick/MS Duo, Memory Stick Micro (M2). With direct USB 2.0 high-speed file transfer (up to 480Mbps) from memory cards used in your digital cameras, cellphone, or MP3 devices, you can save time and conserve power on devices. It also instantly transfers your slotMusic™ songs to your PC or Mac. No matter where you go, IOGEAR's Universal Memory Bank helps you to easily bring your digital images and data with you.

Supporting Media List: - Compact Flash/Micro Drive: CF-Type I, CF-Type II, CF-Ultra II, Microdrive, CF-Pro II, CF-Extreme, CF-Extreme III, CF-PSP II, CF-Supper, CF-Ultra X - SD/SDHC: SD, SDHC, SD-Pro, SD-Pleomax, SD-Pro C, Ultra II SD, Ultra II Plus SD, SD-Extreme III, SD-Ultra X, SD-Turbo, SD-Supper, SD Max, Mini SD, Mini SD-Pro, Mini SD-Pleomax, MMC, MMC-Pleomax, MMC Pro, HS-MMC, MMC Plus, MMC-Plus Turbo, RS MMC, RS MMC-Pleomax, RS MMC-Speed, RS MMC-Max, MMC Mobile, MMC Mobile-ProC, MMC Mobile-Pocketnet, MMC Micro* - Olympus DC Card: Olympus DC Card, Olympus DC Card(M), Olympus DC Card (H) - microSD/microSDHC: microSD/microSDHC, T-Flash - Memory Stick: MS, MS-Magic Gate, MS-PRO Magic Gate, HS-MS-PRO Magic Gate, MS-DUO, MS DUO Magic Gate, MS-PRO Duo, HS-MS-PRO Duo, HS-MS-PRO Duo Magic Gate, MS-PRO Duo-PSP, MS-PRO Duo-Gaming Memory Stick - M2: Memory Stick Micro (M2)

* Adapter required.

- Easy installation; Plug-n-Play
- Reads and writes multiple media cards at one time
- **CompactFlash Type I, II**
- **High Capacity support:** SDHC/microSDHC
- SD/Mini SD/MMC/microSD/T-Flash, transfer your slotMusic™ songs to your PC or Mac
- **Olympus and Fuji Film flash memory**
- **Memory Stick/MS Duo**
- **Memory Stick Micro (M2)**
- Remarkable high-speed digital image and data transfer to computer
- USB 2.0 transfer speeds up to 480Mbps.
- No power adapter needed
- Works with all popular memory cards without additional adapters required
- Specifically designed for digital cameras and also ideal for using with Palmtop PCs, Handheld PCs, PDAs, Voice Recorders and other mobile electronics
- Hot swapping capacity for replacing PC storage cards without restarting the computer



Requirements

- Windows(R) 7, Windows 8.1, 10, 11
 - Available USB 2.0 port
 - Chrome Book
 - Mac OS 10.11+
 - Linux®, Unix and other USB supported systems*
- *Additional drivers and support may be needed

* Windows XP® systems require [this Microsoft update](#) to support SDXC cards

Package Contents

- 1 x 56-in-1 Card Reader/Writer
- 1 x USB Cable (Type A - mini B)
- 1 x Quick Start Guide

Specifications

Function	GFR281
Housing	
Case	Plastic
Ports	(1) USB mini-B port
Operating Temperature	- 40 ~ + 176 ° F (- 40 ~ + 80 ° C)
Storage Temperature	+ 32 ~ + 158 ° F (0 ~ + 70 ° C)
Operating System Support	Win 2000, XP, Vista, MAC 10.11+
USB Specification	USB 1.1 and 2.0 compliant
Transfer Rate	480 Mbps
Humidity	20-80% RH, (Non Condensing)
Cable Type	1 - USB 2.0 Cable (Type mini-B to A) 3-feet
Power Mode	Bus Powered

Dimensions	GFR281
POP Information	
10" Peg Hook	5
6" Peg Hook	3
Unit Dimensions	
Height	0.625 in.
Length	4 in.
Depth	2.3 in.
Inner Pack	
Height	7.5 in.
Length	10 in.
Width	6.75 in.
Inner Pack Qty.	6
Unit Package Dimensions	
Height	10.25 in.
Length	6.75 in.
Width	2.25 in.
Master Carton	
Height	14 in.
Width	10 in.
Depth	15.5 in.
Master Carton Qty.	24
Weight	
Master Carton Wt.	11 lb.
Inner Pack Wt.	2.6 lb.
Unit Pack Wt.	0.5 lb.
Unit Wt. w/accessories	0.28 lb.
Unit Wt.	0.25 lb.