

# Product data sheet

Specifications

SQUARE D

Green Premium™



Transformer, Type TF, industrial control, 250VA, 240x480VAC primary, 120VAC secondary, 1 phase, 50/60Hz, 80°C rise

9070TF250D1

Product availability : Stock - Normally stocked in distribution facility

Price\* : 287.00 USD

## Main

Product or Component Type	Industrial Control Transformer
Power Rating	250 VA
Primary Voltage	220 x 440 V 240 x 480 V 230 x 460 V
Secondary Voltage	110 V 115 V 120 V
Type	TF

## Complementary

Number of Phases	1 phase
Power Rating	250 VA UL 250 VA CSA 250 VA NOM 160 VA
Primary to Secondary Voltage	220 x 440 V 110 V 230 x 460 V 115 V 240 x 480 V 120 V
Fuse type	0.41 x 1.50 in CC top
Temperature rise	80 °C
Electrical Connection	Screw clamp terminals
Height	4.5 in (114.30 mm)
Width	3.75 in (95.25 mm)
Depth	5.3 in (134.62 mm)
Material	Copper winding
Fingersafe Cover Compatibility	FSC2

## Environment

Product certifications	CSA file LR37055 guide 184-N-90 UL listed file E61239
Enclosure Type	Not rated (open device)
Insulation temperature	266 °F (130 °C)

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Ordering and shipping details

Category	16203-9070 TF (NOT T) 250-1000VA
Discount Schedule	CP8
GTIN	785901904861
Nbr. of units in pkg.	1
Package weight(Lbs)	8.30 lb(US) (3.765 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	6.50 in (16.51 cm)
Package 1 width	6.80 in (17.272 cm)
Package 1 Length	7.60 in (19.304 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------