# 811K/6A **DIGITAL HIGH PERFORMANCE TRACING KIT**



TESTING | TROUBLESHOOTING | ACCURACY

#### UNVERSALLY COMPATIBLE.

The 811k/6A Digital High Performance Tracing Kit is a wire and pair tracing tool that is both universally compatible and virtually noise-immune. Whether tracking wires in a clear and guiet location or trying to find a wire in an area roaring with power hum and digital crosstalk, the 200XP probe and 77GX2 tone generator work efficiently. The tracing pair is also capable of working with any older type conventional tone probes and tone generators.

## Features:

- High noise immunity.
- Adjustable to a wide range of applications.
- Flexible connection.
- ID577™ compatible.
- Universally compatible with older equipment.

### **ORDERING INFORMATION:**

CAT. NO.	DESCRIPTION	
811K/6A	Digital High Performance Tracing Kit	















## 811K/6A INFORMATION

#### **Product Features:**

- Trace wire pairs or cables even in areas with high electrical noise levels.
- Very high performance together, still work with all older tracing equipment.
- Crystal-controlled digital signal processing (DSP) accuracy.
- Selectable digital probe filtering allows users to choose performance.
- Single button probe function control.
- Power hum melts away with the press of a button.
- Works with butt sets for improved audibility in loud locations

- Selectable power output levels in generator permit tailoring to application.
- Two-line telephone service indication.
- Short circuit check.
- Tone generator offers modular plug, modular jack or ABN alligator clip connection.
- Three selectable tone sending patterns.
- Auto-off battery saver function for probe (5 min) and generator (4 h).
- Low battery indication.

#### **SPECIFICATIONS:**

TONE PROBE		
Probe tip resistance:	300 ohms minimum	
Filter 2 out-of-band rejection:	30dB	
Input impedance:	100M ohms	
Gain:	35 decibels	
Power:	One 9V battery, nominal life >50 h	
Battery-saver time out:	5 minutes	
Size:	1.25 x 1.375 x 9.75 inches	
Weight:	Weight 4.7 ounces with battery	

TONE GENERATOR		
Output Voltage (Talk Battery into 600 ohms):	5.5 Vdc	
Output Signal Power (600 ohms):	Hi Setting +8 dBm Low Setting +1 dBm	
Output Frequency (nominal):	Tone alternating 577/984 Hz+/-1%	
Output Warble Rate:	Slow 2.5 Hz Medium 6 Hz Fast 13 Hz	
Output Voltage Protection:	60 Vdc	
Power:	One 9V battery, nominal life >100 h	
Auto Shut-Off (in Tone mode):	4 hours	
Size:	4.0 x 1.65 x 1.5 inches 10.1 x 4.2 x 3.8 cm	

1390 Aspen Way Vista, CA • 92081

TC811/6A 03/21

Latin America Phone : 1.760.510.0558 | EMEA Phone: +44 (0) 1633 927050 @2020 Tempo Communications Inc. • An ISO 9001 Company

EMEA Office: Tempo Europe Limited

Brecon House, William Brown Close, Cwmbran • NP44 3AB, UK













**TEMPO**°