

Eaton Freedom NEMA motor control starter

A200M1CAC

UPC:786678231167

Dimensions:

- **Height:** 3.31 IN
- **Length:** 4.61 IN
- **Width:** 4.38 IN

Weight:2.6 LB

Notes:For ambient compensated overload relay with auto-reset, add Suffix D.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Series:** A200
- **Special Features:** Wired for separate control
- **Amperage Rating:** 27A
- **Max Hp Rating:** 2 hp at 115V, 7-1/2 hp at 208,240V, 10 hp at 480,600V
- **Number Of Poles:** Three-pole
- **Phase:** Three-phase magnetic
- **Size:** 1

Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)
- [Eaton Specification Sheet - A200M1CAC](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.