

Eaton 10250T pushbutton

10250T297LGP24

UPC:782114712252

Dimensions:

- **Height:** .01 IN
- **Length:** .01 IN
- **Width:** .01 IN

Weight:.01 LB

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Heavy-Duty Watertight/Oiltight
- **Actuator:** PresTest
- **Light Unit Type:** LED, full voltage
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Lens Color:** Green
- **Lens Material:** Plastic
- **Light Unit Voltage:** 24 Vac/dc
- **Series:** 10250T

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T297LGP24](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance:

- CE Marked