

## Enclosed Precision Limit Switch

**E47BLS06**

**UPC:**782113771113

**Dimensions:**

- **Height:** 2.91 IN
- **Length:** 3.39 IN
- **Width:** 1 IN

**Warranties:**

- 1 year

**Specifications:**

- **Connection:** Screw Terminals
- **Contact Rating:** 15A at 250 Vac, 6A at 30 Vdc
- **Actuator:** Booted plunger
- **Contact Configuration:** 1-SPDT (Form C)
- **Enclosure Material:** Die cast aluminum
- **Environmental Rating:** NEMA 1
- **Maximum Ac Current:** 15A
- **Operating Speed:** 0.01 mm/s-1m/s
- **Operating Temperature:** -13° to 176°F (-25° to 80°C)
- **Series:** E47

**Supporting documents:**

- [Eatons Volume 8-Sensing Solutions](#)
- [E47 precision - Limit switches](#)
- [Eaton Specification Sheet - E47BLS06](#)

**Certifications:**

- CSA Certified
- UL Listed

**Product compliance:** No Data