

Eaton E50 NEMA heavy duty plug-in limit switch

E50BT2

UPC:782113361857

Dimensions:

- **Height:** 1.78 IN
- **Length:** 5.18 IN
- **Width:** 1.54 IN

Warranties:

- 1 year

Specifications:

- **Type:** Assembly
- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 240 Vac, 1A at 250 Vdc
- **Actuator:** Top pushbutton
- **Contact Configuration:** 2NO-2NC
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Maximum Ac Current:** 10A continuous
- **Maximum Dc Current:** 1A
- **Operating Temperature:** 14° to 201°F (-10° to 94°C)
- **Series:** E50

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50BT2](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data
