

Product Specification



LG

Model
32LQ630B6



Audio

Audio power 10 W
Sound technology AI sound
Speakers 2
Other features Clear Voice Pro

Connectivity

Audio output Optical x 1
Connections
- HDMI 1.4 x 2 (eARC compatible) - USB 2.0 x 1
WiFi Built-in WiFi
Ethernet Yes
Bluetooth Bluetooth 5.0

Screen

Screen technology LED directlit
Resolution HD Ready 1366 x 768p
Screen size 32"
HDR - HDR10 - Hybrid Log Gamma (HLG)
HDR technology Active HDR
Motion rate 50 Hz
Picture enhancement Resolution upscaler
Processor α5 Gen5 AI Processor
Refresh rate 60 Hz

Gaming technology

- Game Optimiser - HGiG

Tuner

Electronic programme guide 8-day EPG and 7-day catch up with Freeview Play

TV tuner

- Freeview HD - Freesat HD Please note: Some services are only available in the UK.

Table-top stand Yes
VESA mount 200 x 200

Smart

Smart TV services

- Catch up TV: BBC iPlayer, ITV Hub, All 4, My5, UKTV
- Streaming: Prime Video, Britbox, Disney+, Google Play, Netflix, NOW TV
- Music: Apple Music, Spotify
- App store: LG Content Store
- Custom homepage
- Full internet browser
- Social media: YouTube, Twitch
Screen mirroring - Miracast (Android)
- Airplay 2 (iOS)
Smartphone app LG ThinQ app

Other smart features

Compatible with LG Magic Remote (sold separately) -
Works with Amazon Alexa & Google Assistant
speakers
Smart platform webOS

General

Colour Ceramic black
Internal menu languages 37 languages

Weight

TV with stand: 4.7 kg
TV: 4.65 kg
Boxed: 5.9 kg

Dimensions

TV with stand: 464 x 736 x 180 mm (H x W x D)
TV: 437 x 736 x 82.9 mm (H x W x D)
Boxed: 510 x 812 x 142 mm (H x W x D)

Box contents

- LG 32LQ630B6LA.AEK 32" Smart HD Ready HDR LED TV - Stand - Remote control - Batteries - Screws - User manual