

TMS PSU 3A BS

Art. Number 318167



PSU 100-240V AC 50/60Hz to 18V DC 3A, UK socket

Our Power Supply Units deliver 18V DC to your cascade system.

Power can be inserted into any TRIAX cascade Multiswitch, Tap, Splitter or Amplifier.

Suitable for small to large systems.

Technical Specifications

ORDER INFORMATION

EAN Number 5702663181670

OPERATIONAL

AC Supply voltage VAC	100...240 VAC
PSU output DC voltage VDC	18 VDC
PSU output max. DC current mA	3000 mA
Control LEDs	Green LED (Power)
Temperature - operating °C	-20...+55 °C
Temperature - storage °C	-10...55 °C

CONNECTORS

Power connector	UK main plug
Connector Type	F-male
Connector DC	1830 ± 50mm DC lead length 1800mm Main cord length

MECHANICAL

Dimensions product (H x D x W) mm	33,8 x 128 x 54,3 mm
Packing QTY	1
Product Height mm	122 mm



TRIAx

connecting the future

Technical Specifications

Product Width mm	55 mm
Product Depth mm	35 mm
Packaging Height m	0.055 m
Packaging Width m	0.220 m
Packaging Depth m	0.095 m
Packaging Volume m3	0.001 m3
Net Weight kg	0.530 kg
Tara Weight kg	0.050 kg
Total Weight kg	0.580 kg
Remarks	Power cord, PSU holder + 4 screws & wall plug short circuit, overload current & voltage protection