

Logic Plus™

mkelectric.co.uk



Plateswitches

DP FLUSH
20 AMP



K4867WHI



K4868WHI

Lockable Fire Alarm Isolator Switch

DP FLUSH
20 AMP



K4780WHI

Architrave Switches

FLUSH
10 AMP



K4841WHI



K4842WHI



K4848BWHI



K4848PWHI

Wide Rocker Switches

FLUSH
10 AMP



K4781GRA



K4782GRA



K4783WHI



K4785WHI

K4867WHI 10
1 GANG DP
K4868WHI 10
2 GANG DP

MOUNTING BOXES

866ZIC

DIMENSIONS

86 x 86mm

FIXING CENTRES

60.3mm

BS EN 60669-1:1999

K4780WHI 1
20A DP LOCKABLE FIRE
ALARM ISOLATOR SWITCH

MOUNTING BOXES

866ZIC

DIMENSIONS

86 x 86mm

FIXING CENTRES

60.3mm

BS 60669-2-4:2005

K4841WHI 5
1 GANG SP
TWO-WAY

K4842WHI 5
2 GANG SP
TWO-WAY

K4848BWHI 5
1 GANG SP PUSH SWITCH
WITH BELL SYMBOL

K4848PWHI 5
1 GANG SP PUSH SWITCH
MARKED 'PRESS'

MOUNTING BOXES

FLUSH

1 GANG: 3921ZIC

2 GANG: 3922ZIC

SURFACE

1 GANG: k2151WHI

2 GANG: k2152WHI

These switches do not have to be derated when used with fluorescent or inductive loads.

K4841, K4842 These switches can be wired as either one-way or two-way.

DIMENSIONS

1 GANG: 86 x 32mm;

2 GANG: 146 x 32mm

FIXING CENTRES

1 GANG: 60.3mm;

2 GANG: 120.6mm

BS EN 60669-1:1999

K4781WHI 10
K4781GRA 10
1 GANG SP TWO-WAY
WITH WIDE ROCKER

K4782WHI 10
K4782GRA 10
2 GANG SP TWO-WAY
WITH WIDE ROCKERS

K4783WHI 10
3 GANG SP TWO-WAY
WITH WIDE ROCKERS

K4785WHI 10
K4785GRA 10
1 GANG SP INTERMEDIATE
WITH WIDE ROCKER

K4787WHI 10
1G 20A DP ONE-WAY
WITH WIDE ROCKER

K4788WHI 10
2 GANG DP WITH
WIDE ROCKER

MOUNTING BOXES

FLUSH

861ZIC

SURFACE

K2160WHI

K2140WHI (for extra

wiring space)

These switches do not have to be derated when used with fluorescent or inductive loads.

DIMENSIONS

86 x 86mm

FIXING CENTRES

60.3mm

BS EN 60669-1:1999

20A DP VERSIONS

K4787WHI is 20A DP

1 way version of K4781.

BS EN 60669-1: 1999

K4788WHI is 20A DP

1 way version of K4782.

BS EN 60669-1:1999