

G33BT

Bluetooth Gaming Headset



 **LOW LATENCY**

 **24H PLAYBACK TIME**

 **NdFeB DRIVER**

 **GAME MUSIC**

 **RGB Lighting**

 **Comfortable Design**

Features

- Lightweight design with soft leatherette ear pads for all-day comfort
- Equipped with gaming and music sound effects and professional tuning to fit various scenarios
- PixArt Bluetooth V5.0 with latency as low as 60ms, compatible with Android and iOS
- Up to 24 hours battery life per charge
- Gradually varied colors based on RGB dynamic backlight technology
- 40mm NdFeB drivers deliver crystal-clear sound and solid bass
- 6mm detachable and flexible omni-directional noise cancelling microphone



Specifications	
Bluetooth version	V5.0
Audio codec	SBC
Playback time	about 24 hours (light on)/about 48 hours (light off)
Charging time	about 2 hours
Battery capacity	750mAh
Frequency response	20Hz-20kHz
Impedance	32Ω
Sensitivity	100dB
Audio inputs	Bluetooth/AUX
Charging port	USB Type-C

**The specifications and functions are subject to the finalized product on the market.*

G33BT

Package & Accessories



*Paper headset stand included in the box.



Box content

- Headset × 1
- Microphone × 1
- 3.5mm-3.5mm audio cable × 1 (1.3m)
- Charging cable × 1
- User manual × 1



Package Info

Product Weight	270g (net weight)
Inner Carton	210×100×235mm (L×W×H), 495g (gross weight)
Master Carton	518×488×453mm (L×W×H), 11.5kg (gross weight)
PCS/CTN	20

Color Options	EAN code
Black	6923520242788
Grey	6923520242795