

Albany Plus™

mkelectric.co.uk



Cooker Control Unit

DP MAIN SWITCH
AND 13 AMP
SWITCHSOCKET
OUTLET WITH NEONS

45 AMP

Triple Pole & Neutral Switch

32 AMP

Shaver/Toothbrush Supply Units

DUAL VOLTAGE
115/230V OUTPUT
220/240V INPUT
50/60HZ

Flex Outlets (NON UK)

Plateswitches

SP
2 WAY
10 AMP



FINISHES

BRUSHED STAINLESS STEEL	K5261BSS	1	K5114BSS	1	K703BSS	1	K2240BSS	1	K4671BSS	5
BRUSHED CHROME	K5261BRC	1	K5114BRC	1	K703BRC	1	K2240BRC	1	K4671BRC	1
SATIN GOLD	K5261SAG	1	K5114SAG	1	K703SAG	1			K4671SAG	1
POLISHED CHROME	K5261PCR	1	K5114PCR	1	K703PCR	1			K4671PCR	1

LEAD TIMES
Please contact our Customer
Services Department on
01268 563 404

MOUNTING BOXES
FLUSH
86ZIC
(Up to 6mm² conductor)
87ZIC
(Up to 10mm² conductor)
Rotary operated shutter.
DIMENSIONS
86 x 146mm
FIXING CENTRES
120.6mm
BS 4177:1992

MOUNTING BOX
FLUSH
878ZIC
This product is rated at
440 volts with a motor load
rating of up to 12kW – 16 HP
at 415V 3 phase.
It has a utilisation category of
AC22A – switching of mixed
resistive and inductive loads
including moderate overloads
for a continuous duty of 32
amps. Making capacity is 2000
amps peak.
TERMINAL CAPACITY
16mm² conductors.
DIMENSIONS
146 x 86mm
BS EN 60947-3:1992

MOUNTING BOXES
FLUSH
878ZIC
This design incorporates
a double wound isolating
transformer rated 20VA at 230
or 115 volts and meets
BS EN 61558-2-5:1998
making it safe for use in
bathrooms.
Insertion of a shaver/
toothbrush plug automatically
switches on by energising the
primary side of the isolating
transformer – removal
automatically switches
off. The transformer is
protected against overload
by an automatic solid state
overload device with automatic
resetting.
DIMENSIONS
146 x 86mm
FIXING CENTRES
120.6mm
BS EN 61558-2-5:1998

MOUNTING BOXES
FLUSH
866ZIC
SURFACE
WITH KNOCKOUTS
K899ALM
SURFACE WITHOUT
KNOCKOUTS
K829ALM
CABLE DIAMETER
Minimum 4mm
Maximum 14.5mm
DIMENSIONS
1 gang: 86 x 86mm
FIXING CENTRES
1 gang: 60.3mm
BS 5733:2010

MOUNTING BOXES
FLUSH
3995ZIC
SURFACE
WITH KNOCKOUTS
K899ALM
SURFACE WITHOUT
KNOCKOUTS
K829ALM
These switches do not have
to be derated when used with
fluorescent or inductive loads.
Switches can be wired as
either one-way or two-way.
DIMENSIONS
86 x 86mm
FIXING CENTRES
60.3mm
BS EN 60669-1:1999
If an intermediate switch is
required, a modular (Grid Plus)
version is available. Order
K3431 grid plate, K3701 grid
frame and K4893WHI 20A
intermediate switch