



Technical Hotline  
+44 (0)1268 563720

# Masterseal Plus™

WIRING DEVICES  
INGRESS PROTECTED IP66

## Switchsocket Outlets, Timer Socket Outlets, and Key Operated Socket Outlets

13 AMP  
IP66

RCD PROTECTED  
13 AMP  
IP66

## Socket Outlets

13 AMP  
IP66

16 AMP  
IP66  
(NON UK)



K56486GRY



K56482BLK



K56488GRY



K56485GRY



K56485WHI



K56487GRY



K56301GRY



K56231BLK



K56233WHI



K56480GRY



K56481WHI



K56481BLK



K56483GRY



K56483WHI



K56483BLK

**K56486GRY** 1  
**K56486WHI** 1  
**K56486BLK** 1  
13A DP  
1 GANG SWITCHED  
**K56482GRY** 1  
**K56482WHI** 1  
**K56482BLK** 1  
13A DP  
2 GANG SWITCHED  
**K56488GRY** 1  
**K56488WHI** 1  
**K56488BLK** 1  
13A DP SWITCHED  
2 GANG  
NEON  
CLEAR COVER

Fixing holes are for No.8 woodscrews (not supplied).

**K56486** has 4 x 20mm entries, 1 on top, bottom and each side and is supplied with an earth terminal in the back box.

2 gang backbox has 5 cable entries, 2 on top and 1 centrally on other 3 sides. Supplied with earth terminals in backbox.

### DIMENSIONS

**1 gang** 157 x 110 x 89mm  
**2 gang** 157 x 175 x 89mm  
BS 1363-2:1995  
IP66 BS EN 60529:1992

**K56485GRY** 1  
**K56485WHI** 1  
**K56485BLK** 1  
13A SP  
1 GANG  
WITH ELECTRONIC  
TIMER MODULE  
**K56487GRY** 1  
**K56487WHI** 1  
**K56487BLK** 1  
13A 1 GANG DP  
KEY OPERATED SOCKET

Timer Module meets the requirements of IEC 60730-1 and IEC 60730-2-7 Standards

**K56301GRY** 1  
**K56301WHI** 1  
**K56301BLK** 1  
1 GANG DP  
30mA RATED TRIPPING  
CURRENT ACTIVE  
CONTROL CIRCUIT  
**K56231GRY** 1  
**K56231WHI** 1  
**K56231BLK** 1  
2 GANG SP  
30mA RATED TRIPPING  
CURRENT ACTIVE  
CONTROL CIRCUIT  
**K56233GRY** 1  
**K56233WHI** 1  
**K56233BLK** 1  
2 GANG SP  
30mA RATED TRIPPING  
CURRENT PASSIVE  
CONTROL CIRCUIT

RCD protected sockets are pulsating d.c. and a.c. fault current sensitive. Fixing holes are for No.8 woodscrews (not supplied).

Supplied with an earth terminal in the back box. The Sentriesocket has 5 entries. Suitable for supply voltage of 240V a.c.

Standard Shutters.

### DIMENSIONS

157 x 175 x 89mm  
BS 7288:1990  
IP66 BS EN 60529:1992

**K56480GRY** 1  
**K56480WHI** 1  
**K56480BLK** 1  
13A 1 GANG  
UNSWITCHED  
**K56481GRY** 1  
**K56481WHI** 1  
**K56481BLK** 1  
13A 2 GANG  
UNSWITCHED

Fixing holes are for No.8 woodscrews (not supplied).

**K56480** has 4 x 20mm entries, 1 on top, bottom and each side and is supplied with an earth terminal in the back box.

BS 1363-2:1995

IP66 BS EN 60529:1992

**K56481** Backbox has 5 cable entries, 2 on top and 1 centrally on other 3 sides. Supplied with earth terminals in backbox.

### DIMENSIONS

**1 gang** 157 x 110 x 89mm  
**2 gang** 157 x 175 x 89mm  
BS 1363-2:1995  
IP66 BS EN 60529:1992

**K56483GRY** 1  
**K56483WHI** 1  
**K56483BLK** 1  
16A  
1 GANG  
2P+E  
UNSWITCHED  
(NON UK)

Fixing holes are for No.8 woodscrews (not supplied).

**K56483** is for use with plugs having right angled cable exit.

### DIMENSIONS

157 x 110 x 89mm  
IEC 60884-1:2006  
IP66 BS EN 60529:1992

Masterseal Plus™ enclosures are manufactured from polycarbonate. This provides an extremely high level of impact resistance. However some chemicals and synthetic oils can harm polycarbonate. Refer to chemical resistance table on page 553.