



Technical Hotline
+44 (0)1268 563720

Masterseal Plus™

WIRING DEVICES
INGRESS PROTECTED IP66

Switchsocket Outlets, Timer Socket Outlets, and Key Operated Socket Outlets

13 AMP
IP66

RCD PROTECTED
13 AMP
IP66

Socket Outlets

13 AMP
IP66

16 AMP
IP66
(NON UK)



K56486GRY



K56482BLK



K56488GRY



K56485GRY



K56485WHI



K56487GRY



K56301GRY



K56231BLK



K56233WHI



K56480GRY



K56481WHI



K56481BLK



K56483GRY



K56483WHI



K56483BLK

K56486GRY 1
K56486WHI 1
K56486BLK 1
13A DP
1 GANG SWITCHED
K56482GRY 1
K56482WHI 1
K56482BLK 1
13A DP
2 GANG SWITCHED
K56488GRY 1
K56488WHI 1
K56488BLK 1
13A DP SWITCHED
2 GANG
NEON
CLEAR COVER

Fixing holes are for No.8 woodscrews (not supplied).

K56486 has 4 x 20mm entries, 1 on top, bottom and each side and is supplied with an earth terminal in the back box.

2 gang backbox has 5 cable entries, 2 on top and 1 centrally on other 3 sides. Supplied with earth terminals in backbox.

DIMENSIONS

1 gang 157 x 110 x 89mm
2 gang 157 x 175 x 89mm
BS 1363-2:1995
IP66 BS EN 60529:1992

K56485GRY 1
K56485WHI 1
K56485BLK 1
13A SP
1 GANG
WITH ELECTRONIC
TIMER MODULE
K56487GRY 1
K56487WHI 1
K56487BLK 1
13A 1 GANG DP
KEY OPERATED SOCKET

Timer Module meets the requirements of IEC 60730-1 and IEC 60730-2-7 Standards

K56301GRY 1
K56301WHI 1
K56301BLK 1
1 GANG DP
30mA RATED TRIPPING
CURRENT ACTIVE
CONTROL CIRCUIT
K56231GRY 1
K56231WHI 1
K56231BLK 1
2 GANG SP
30mA RATED TRIPPING
CURRENT ACTIVE
CONTROL CIRCUIT
K56233GRY 1
K56233WHI 1
K56233BLK 1
2 GANG SP
30mA RATED TRIPPING
CURRENT PASSIVE
CONTROL CIRCUIT

RCD protected sockets are pulsating d.c. and a.c. fault current sensitive. Fixing holes are for No.8 woodscrews (not supplied).

Supplied with an earth terminal in the back box. The Sentriesocket has 5 entries. Suitable for supply voltage of 240V a.c.

Standard Shutters.

DIMENSIONS

157 x 175 x 89mm
BS 7288:1990
IP66 BS EN 60529:1992

K56480GRY 1
K56480WHI 1
K56480BLK 1
13A 1 GANG
UNSWITCHED
K56481GRY 1
K56481WHI 1
K56481BLK 1
13A 2 GANG
UNSWITCHED

Fixing holes are for No.8 woodscrews (not supplied).

K56480 has 4 x 20mm entries, 1 on top, bottom and each side and is supplied with an earth terminal in the back box.

BS 1363-2:1995

IP66 BS EN 60529:1992

K56481 Backbox has 5 cable entries, 2 on top and 1 centrally on other 3 sides. Supplied with earth terminals in backbox.

DIMENSIONS

1 gang 157 x 110 x 89mm
2 gang 157 x 175 x 89mm
BS 1363-2:1995
IP66 BS EN 60529:1992

K56483GRY 1
K56483WHI 1
K56483BLK 1
16A
1 GANG
2P+E
UNSWITCHED
(NON UK)

Fixing holes are for No.8 woodscrews (not supplied).

K56483 is for use with plugs having right angled cable exit.

DIMENSIONS

157 x 110 x 89mm
IEC 60884-1:2006
IP66 BS EN 60529:1992

Masterseal Plus™ enclosures are manufactured from polycarbonate. This provides an extremely high level of impact resistance. However some chemicals and synthetic oils can harm polycarbonate. Refer to chemical resistance table on page 553.