

Logic Plus™

mkelectric.co.uk



Socket Outlets

FLUSH
13 AMP

ROUND PIN
FLUSH

127V
FLUSH
15 AMP
(NON UK)



K780WHI



K781WHI



K781RED



K770WHI



K771WHI



K772WHI



K2251WHI



K2252WHI

K780WHI 10

1 GANG

K781WHI 5

2 GANG

WITH DUAL EARTH
TERMINALSMOUNTING BOXES
FLUSH 25MM

1 GANG: 861ZIC

2 GANG: 862ZIC

FLUSH 35MM

(for extra wiring space)

1 GANG: 866ZIC

2 GANG: 886ZIC

SURFACE

1 GANG: K2140WHI

2 GANG: K2142WHI

K781 is fitted with two earth terminals to provide a double
earth facility for use when installations require a high
integrity protective connection as specified within
BS 7671 IET Wiring Regulations

DIMENSIONS

1 GANG: 86 x 86mm

2 GANG: 86 x 146mm

FIXING CENTRES

1 GANG: 60.3mm

2 GANG: 120.6mm

BS 1363: Pt2:1995

K770WHI 10

1 GANG

2A SHUTTERED

K771WHI 10

1 GANG

5A SHUTTERED

K772WHI 10

1 GANG

15A SHUTTERED

MOUNTING BOXES

FLUSH

861ZIC (25mm)

866ZIC

(35mm for extra wiring space)

SURFACE

K2140WHI

DIMENSIONS

86 x 86mm

FIXING CENTRES

60.3mm

BS 546:1950

K2251WHI 10

1 GANG

SHUTTERED

(NON UK)

K2252WHI 5

2 GANG

SHUTTERED

(NON UK)

MOUNTING BOXES

FLUSH 25MM

1 GANG: 861ZIC

2 GANG: 862ZIC

FLUSH 35MM

(for extra wiring space)

1 GANG: 866ZIC

2 GANG: 886ZIC

SURFACE

1 GANG: K2140WHI

2 GANG: K2142WHI

DIMENSIONS

1 GANG: 86 x 86mm

2 GANG: 86 x 146mm

FIXING CENTRES

1 GANG: 60.3mm

2 GANG: 120.6mm

SASO 2204:2003