

Commando

mkelectric.co.uk



IP44
 SPLASHPROOF
 200 - 250V
 50 - 60 HZ

Plugs

Connectors

Socket Outlets

ANGLED
 SURFACE

SURFACE-LOOP IN

STRAIGHT
 PANEL MOUNTING

Amps	Pin. Config- uration	Earth					
16	2P+E	6	K9001BLU	K9101BLU	K9201BLU	K13301BLU	K9401BLU
16	3P+E	9	K9006BLU	K9106BLU	K9206BLU		
16	3P+N+E	9	K9014BLU	K9114BLU	K9214BLU		
32	2P+E	6	K9033BLU	K9133BLU	K9233BLU	K13333BLU	K9433BLU
32	3P+E	9	K9036BLU	K9136BLU	K9236BLU		
32	3P+N+E	9	K9044BLU	K9143BLU	K9240BLU		
63	2P+E	6	K9063BLU	K9172BLU	K9274BLU		K9472BLU

16A/32A
 Fitted with cable entry gland.
 63A
 Fitted with cable entry gland
 BS EN 60309

16A/32A
 Fitted with cable entry gland.
 63A
 Fitted with cable entry gland
 BS EN 60309

16A Top conduit (M20) or rear
 cable entry, complete with
 blanking plug.
 32A Top conduit (M25) or rear
 cable entry, complete with
 blanking plug.
 63A Top conduit (M32) or rear
 cable entry, complete with
 blanking plug
 BS EN 60309

Suitable for top entry 1 x M20
 and 1 x M25 or bottom entry
 1 x M20 and 1 x M25
 BS EN 60309

16/32A
 All flanges have the same
 fixing centres and outside
 dimensions to assist panel
 builders
 BS EN 60309

Plugs

Connectors

Socket Outlets

ANGLED
 SURFACE

SURFACE – LOOP IN

Amps	Pin. Config- uration	Earth				
16	2P+E	6	K9024BLU	K9124BLU	K9194BLU	K13024BLU
16	3P+E	6	K9081BLU	K9082BLU	K9083BLU	
32	2P+E	6	K9054BLU	K9156BLU	K9762BLU	K13054BLU
32	3P+E	6				
63	2P+E	6	K9298BLU	K9856BLU	K9857BLU	

Suitable for flexible cable only
 63A. With external clamp
 BS EN 60309

Suitable for flexible cable only
 63A. With external clamp
 BS EN 60309

Suitable for top entry 2 x M25
 or bottom entry 2 x M20.
 Will accept FL13 flange at top
 BS EN 60309

Suitable for top entry 1 x M20
 and 1 x M25 or bottom entry
 1 x M20 and 1 x M25
 BS EN 60309