

IRT150 Stem Thermometer + IR

Built-in fold-out probe for quick & accurate measurements

Features:

- Use non-contact IR for surface temperatures or stem probe for internal temperatures
- High/Low alarms
- Backlit display for use in poorly lit areas
- HACCP approved
- Waterproof (IP65)
- Built-in flashlight
- Includes (2) AAA batteries

Applications:

For industrial use for measuring food temperatures in HACCP designated safety zones and for home use

Specifications

IR Temperature	-4 to 536°F (-20 to 280°C)
Response Time	<500ms
Distance to Target Ratio	4:1
Emissivity	0.95
Thermistor Temperature	32 to 392°F (0 to 200°C)
Basic Accuracy	±1%
Resolution	0.1°F/°C
Waterproof	IP65
Power	(2) AAA Batteries
Dimensions	7.3 x 2.6 x 2" (185 x 67 x 50mm)
Weight	6.5oz (180g)



Ordering Information:

IRT150 Stem Thermometer + IR